

DT HIGHSPEED CONNECTORS

Key	Color	Sockets		Pins		Headers		
		Housing Assembly	Connector Kit ²	Housing Assembly	Connector Kit ²	Bulkhead Header Assembly	180° PCB Header Assembly	90° PCB Header Assembly
A	Black	9-2367337-1	9-2386764-1	9-2367341-1	9-2386764-1	9-2383999-1	9-2367359-1	2386211-1
B	Gray	9-2367337-2 ¹	-	9-2367341-2 ¹	-	9-2367359-2 ¹	-	-
C	Green	9-2367337-3 ¹	-	9-2367341-3 ¹	-	9-2367359-3 ¹	-	2386211-3
D	Blue	9-2367337-4 ¹	-	9-2367341-4 ¹	-	9-2367359-4 ¹	-	-

Sub-Assemblies			Cover Assemblies	
Socket	Pin	Header (180°, Shielded Pin)	Socket (w/CPA) 0.50 mm ² STP cable O.D.	Socket (w/CPA) 0.35 mm ² STP cable O.D.
9-2370714-1	9-2370710-1	9-2370706-1	9-2367345-1	9-2367345-2

¹Contact TE for more information and availability.

²Kits contain all connector components and terminals to assemble one full connector - cable not included.

SEAL/FERRULE HARDWARE

Description	Part Number	Use With	Mates To
Single Wire Seal, 20 AWG [0.5 mm ²]	9-2367346-1	9-2367345-1 9-2367344-1	Approved STP 0.50 mm ² /20 AWG
Single Wire Seal, 22 AWG [0.35 mm ²]	9-2367346-2	9-2367345-2 9-2367344-3	Approved STP 0.35 mm ² /22 AWG
Crimp Ferrule, 20 AWG [0.5 mm ²]	9-2370624-1	9-2370714-1	Approved STP 0.50 mm ² /20 AWG
Crimp Ferrule, 22 AWG [0.35 mm ²]	9-2370624-2	9-2370710-1	Approved STP 0.35 mm ² /22 AWG
DEUTSCH Socket Size 20 (AWG) Solid Terminal, AU Plating	0462-201-2031	9-2370714-1	0460-202-2031
DEUTSCH Pin Size 20 (AWG) Solid Terminal, AU Plating	0460-202-2031	9-2370710-1	0462-201-2031
DT Mounting Clip, BLK, Fir Tree Stud Mount	1011-310-0205	9-2367341-X	-
Blind Plug, Key - Universal	2384003-1	-	9-2367341-X 9-2367359-X

TOOLING

	Handtools			Benchtop	
	Handtool & Die Set	Handtool Frame only	Die Set only	Benchtop Press	Benchtop Die Set
Benchtop Press	2399600-1	2362810-1	2399600-2	2348822-2	2380176-1
Ferrule 0.35 mm ² STP	Handtool & Die Set	Handtool Frame only	Die Set only	Benchtop Press	Benchtop Die Set
	TBA	2362810-1	TBA	2348822-2	TBA
Size 20 DEUTSCH Terminal	Handtool	Benchtop Die Set	Benchtop Die Set Locator	Benchtop Press	-
	HDT-48-00	414DA-20N.038	400-4301-20S	HDP-400	-