

AXEL

Sato Keiryoki Mfg. Co., Ltd.

61-9437-90 Digital Thermo-Hygrometer with Calibration Report PC-7700II



Order No.	61-9437-90
Model No.	PC-7700II
JAN Code	0000000000000
	JPY: 17,600
	USD: 117.62
Standard price	
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1set

Features

- Easy-to-read temperature and humidity meter with bar graph display
- Maximum and minimum temperature and humidity are always displayed
- Convenient stand attached, can be used for both desk and wall hanging.
- High precision temperature and humidity meter capable of traceability calibration service

Spec

- Calibration point: Temperature 23°C humidity 60% (at 23°C)
- Contents of calibration documents: Calibration report
- Model number: PC-7700II
- Resolution (temperature/humidity): 1°C/1%RH
- Measurement accuracy: Temperature +/- 1°C (10 - 40°C), +/- 2°C (other), Humidity +/- 5%RH (15 - 35°C, 40 - 70%RH), +/- 7%RH (other)
- Material: Body/ABS resin, acrylic (key made of rubber)
- Power supply: R03 AAA manganese battery x 1 (included for test)
- Size: 148 x 68 x 19mm
- Weight: Approximately 150g (including cell)
- Measurement range (temperature/humidity): - 10 - 50°C/20 - 95%RH
- Room navigation