

# AXEL

3M Company

2-9688-02 Connector 38104-0020100FL Black 38104-0020-100FL



|                |                               |
|----------------|-------------------------------|
| Order No.      | 2-9688-02                     |
| Model No.      | 38104-0020-100FL              |
| JAN Code       | 0000000000000                 |
|                | <b>JPY:</b><br><b>420</b>     |
|                | <b>USD:</b><br><b>2.81</b>    |
| Standard price |                               |
|                | Exchange rate 1USD= 149.64JPY |
|                | Valid price in Japan          |
| Quantity       | 1piece                        |

## Spec

- Material: Body/PBT (Polybutylene, terephthalate), Cover/nylon, Contact/copper alloy
- Electric cable type: for flat cable
- Rating voltage: AC/DC160V or less
- Rated current: Maximum 5.0A
- Operating temperature range: -20 - 70°C
- Cover color: Black
- Applicable wire (AWG No.): 20
- Finished outer diameter (φmm): 2.54
- 4 pole
- Model number: 38104-0020-100FL

▫ Package size : 50×50×50 mm 100 g

## Product Catalog

| Catalog Name                                     | Page |
|--|------|
| AS ONE Catalog 2015 [Instruments for Laboratory] | 1630 |