

AXEL

A&D Company, Limited

61-4672-78 K Type Thermocouple Probe AD-1214 AD-1214



Order No.	61-4672-78
Model No.	AD-1214
JAN Code	4981046490108
	JPY: 1,800
	USD: 12.02
Standard price	
	Exchange rate 1USD= 149.78JPY
	Valid price in Japan
Quantity	1piece

Features

- [Application]
 - Various shapes are available for checking the temperature of equipment, checking the temperature of cooking utensils, and measuring the surface temperature.
- 【 Features 】
 - Used by connecting to K-type thermocouple thermometer
 - Suitable for small thermocouple connector (SMP type) of Omega, U.S.A. (spacing of 7.9 mm in the center of the flat electrode)
 - Available in various shapes depending on the application

Spec

- Measurement range (thermosensitive part): -50 to +200°C
- Type of temperature sensor: K type thermocouple
- Structure: Exposure contact type
- Sensor cable length: About 1m (FEP, Teflon)
- Sensor unit dimensions: Contact part about ϕ 1mm
- Handle part: Cable about ϕ 1.8mm x L1m (heat resistance temperature 200°C)
- Accessories: Instruction manual:

▶ Package size : 60×200×15 mm 20 g