

AXEL

ANRITSU METER CO., LTD.

2-1085-03 Extremely Small Surface Thermo-Sensor (400°C Straight K Type) For Portable Thermometer CS-11K-010-1-TC1-ASP



Order No. 2-1085-03
Model No. CS-11K-010-1-TC1-ASP
JAN Code 4562478160373

Standard price
JPY: 20,500
USD: 137.91

Exchange rate 1USD= 148.65JPY
Valid price in Japan

Quantity 1piece



Calibration Available

Features

- <Body>
- It has adopted the thermocouple same metal, it is improved accuracy.
- Characteristic test is done at the time of shipment (attached to examination results book) .
- <Sensor>
- Since it is adopted 4-points of support structure in its contact part, it keeps its support point free without fixing it (2-1089-01) .
- Suitable for temperature measuring of surface that is moving and rotating (2-1086-01, 03.07) .
- It is very thin and flexible, it is multi-purpose sensor tape shape (2-1088-01-03)

Spec

- Model number: CS11K-010-1-TC1ASP
- Type: Minimal surface sensor
- Thermocouple: K
- Temperature range: -50 - 400°C
- Sensor shape: Straight

Package size : 80×300×50 mm 500 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	554
AS ONE Catalog 2021 [Instruments for Laboratory]	510
AS ONE Catalog 2019 [Instruments for Laboratory]	487