

# AXEL

Brookfield

2-2787-21 Brookfield Viscometer XDV2TLVTJ00U00



Order No.	2-2787-21
Model No.	XDV2TLVTJ00U00
	<b>JPY:</b> <b>1,240,000</b>
Standard price	<b>USD:</b> <b>8,341.74</b>
	Exchange rate 1USD= 148.65JPY Valid price in Japan
Quantity	1 unit



Calibration Available

## Features

- Provided with touch panel realizing multiple functions and usability.
- Switchable in 0.1 rpm increments between 0.1~9.9 rpm, and 1 rpm increments between 10~200 rpm allowing fine adjustment of Rotation per minute.
- Allows easy control and data gathering and saving on PC if used with Rheocalc T (sold separately) .

## Spec

- Configurable speed r.p.m. : 0.1 - 200rpm (configurable number of stage: 290)
- Viscosity measurement accuracy:  $\pm 1.0\%$  (F.S.)
- Viscosity reproducibility:  $\pm 0.2\%$  (F.S.)
- Temperature detection range: -100 to +300°C
- Main display items: Viscosity value, torque value, shear speed, shear stress, temperature, spindle, etc.
- Output: USB port
- Power supply: AC90 - 260V 50/60Hz
- Power consumption: 150W
- Main unit size: 360 x 350 x 590mm (maximum)
- Weight: Approx 9kg
- For low viscosity
- Measurement range (mPa · s): 15 - 6,000,000
- Set content: Body, Stand G type, Standard spindle set (LV-1 - 4/1 piece each, RV, HA, HB-2 - 7/1 piece each), Power cable (3P plug), Resistance thermometer RTD, Guard leg (LVDV, RVDV only), Screen cloth, USB memory, Stylus, Cap, Carry case, Software (PG flash software)
- Model number: LVDV2T

▶ Package size : 310×530×430 mm 12.5 kg