

AXEL

1-3556-01 Thermo-Hygro Transmitter Data Logger AC Power HD2717T.DR



Order No.	1-3556-01
Model No.	HD2717T.DR
JAN Code	0000000000000
	JPY: 93,300
	USD: 627.65
Standard price	
	Exchange rate 1USD= 148.65JPY Valid price in Japan
Quantity	1unit

Features

- It is compatible probe, possible to replace it quickly on spot.

Spec

- Model number: HD2717T.DR
- Body (AC90 - 240V)
- Measurement range: Temperature/-50 to +150°C, Humidity/5 - 98%RH
- Accuracy: Temperature/+/- 0.25°C, Humidity/±2.5%RH (5 - 90%RH), ±3.0%RH (90 - 98%RH)
- Sensor: Temperature/Pt100Ω, Humidity/capacitance type
- Display: LCD
- With calculation function (wet sphere/dew point temperature, absolute humidity, mixed ratio)
- Memory: 9000 data
- Memory interval: 1, 2, 5, 10, 20, 60 seconds/2, 4 minutes
- Analog output: 4 - 20mA, 0 - 20mA, DC0 - 10V, DC2 - 10V (switchable)
- Interface: RS232C, RS485 multi-drop
- Supported OS: Windows(R) 98/XP/VistaTM/7
- Power consumption: 3W
- Size: 143 x 61 x 154mm
- Weight: Approx 600g
- Dustproof, waterproof: IP65

▶ Package size : 170×230×80 mm 760 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	603
AS ONE Catalog 2021 [Instruments for Laboratory]	561
AS ONE Catalog 2019 [Instruments for Laboratory]	536