

# AXEL

## 1-3746-01 Thermo-Hygro Transmitter HD9008TRR



Order No.	1-3746-01
Model No.	HD9008TRR
JAN Code	0000000000000
	<b>JPY:</b> <b>79,900</b>
	<b>USD:</b> <b>537.50</b>
Standard price	
	Exchange rate 1USD= 148.65JPY
	Valid price in Japan
Quantity	1unit

### Features

- It is microprocessor-controll.
- Tip portion of its case is equipped with sensor.
- Calibration and scaling can be operated by its key.
- When using transmitter outdoors, the protection food (separate sale) protects it from ultraviolet rays and wind and rain.

### Spec

- Model number: HD9008TRR
- 4 - 20mA output type
- Measuring method: Temperature/Pt100Ω sensor 100Ω, Humidity/capacitance type
- Measurement range: Temperature/-40 to +80°C, Humidity/5 - 98%RH
- Accuracy: Temperature/+/- 0.25°C, Humidity (at 20°C)/+/- 2% (5 - 90%RH), +/- 2.5% (other)
- Power supply: 10 - 40VDC (4 - 20mA)
- Cable length (MAX): 200m
- Size: φ26 x 225mm

▶ Package size : 60×260×40 mm 70 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2019 [Instruments for Laboratory]	536
AS ONE Catalog 2017 [Instruments for Laboratory]	422
AS ONE Catalog 2015 [Instruments for Laboratory]	386