

AXEL

AS ONE Corporation

1-5812-01 Digital Thermometer 1ch TM-300



Order No.	1-5812-01
Model No.	TM-300
JAN Code	4562108502498
	JPY: 14,000
	USD: 93.56
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1unit

Calibration Available

Features

- It is with data hold facility which fixes measuring data.
- It is with max. memory display function which can carry out memory of highest temperature at the time of measuring automatically, and possible to called after measuring.
- Possible to use measuring at dark place for display part in comfort with back light function.
- Since temperature survey of 2-points (T*_{@1@*}-T*_{@2@*}) is possible for TM-301 type and it is also possible to display difference of measured value, it is very at convenience.

Spec

- Model number: TM-300
- Number of inputs: 1
- Measurement range: -50 - 1300°C
- Resolution: 0.1/1°C (switch type)
- Sensor type: K class thermocouple
- Measurement range: -50 - 1300°C
- Body accuracy: -50 - 1000°C/±(0.3%rdg + 1°C), Other/±(0.5%rdg + 1°C)
- Sampling rate: 2.5 times/second
- Display: 3.5 digits LCD display
- Used temperature and humidity: 0 - 50°C, 0 - 80%RH (0 - 35°C)
- Storage temperature: -20 to +60°C
- Power supply: 006P (9V) cell x 1 (included for test)
- Size: 156 x 65.5 x 35mm
- Weight: Approx 177g
- *Sensor probe is sold separately.

▶ Package size : 190×90×50 mm 240 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	556
ASTOOL Catalog 2018>2019 [Indirect Materials for Manufacturing]	74
AS ONE Catalog 2021 [Instruments for Laboratory]	512