

# AXEL

BIP SHOUKO Co., Ltd.

## 3-5521-01 Air Grinder for Intensive Work 140 x 40mm 22000min<sup>-1</sup> PWG-2590



Order No.	3-5521-01
Model No.	PWG-2590
JAN Code	0000000000000
	<b>JPY:</b> <b>14,500</b>
	<b>USD:</b> <b>96.81</b>
Standard price	
	Exchange rate 1USD= 149.78JPY Valid price in Japan
Quantity	1unit

### Features

- Exhaust on this grinder is located in front, and air coupler can be installed directly to body

### Spec

- Model number: PWG-2590
- Size (mm): 140 x 40
- Weight (g): 600
- Rotation speed: 22000 min<sup>-1</sup>
- Exhaust system: forward
- Air pressure: 0.4 to 0.65 MPa
- Air consumption: 0.3 m<sup>3</sup>/min
- Collet: 6mm
- Air connection port diameter: 2 minutes (1/4 inch)

▶ Package size : 165×270×60 mm 770 g

### Product Catalog

Catalog Name	Page
ASTOOL Catalog 2021 > 2022 [Indirect Materials for Manufacturing]	61
ASTOOL Catalog 2018 > 2019 [Indirect Materials for Manufacturing]	69
AS ONE Catalog 2019 [Instruments for Laboratory]	295
AS ONE Catalog 2017 [Instruments for Laboratory]	253
ASTOOL Catalog 2016 > 2017 [Indirect Materials for Manufacturing]	76