

# AXEL

BIP SHOUKO Co., Ltd.

**3-5522-01 Mini Air Grinder DOTCO (R) 146 x 17mm 60000 min<sup>-1</sup> 10R**



Order No.	3-5522-01
Model No.	10R
JAN Code	0000000000000
	<b>JPY:</b> <b>79,000</b>
	<b>USD:</b> <b>527.44</b>
Standard price	
	Exchange rate 1USD= 149.78JPY
	Valid price in Japan
Quantity	1unit

## Features

- Compact and light structure of this grinder allows you to control tool easily, and reach spots that are far in back of workpiece.
- It is stainless steel and brass structure offers excellent corrosion protection.
- Rotary throttle enables stepless speed control.
- Special high-precision collet allows you to operate machine smoothly, and keeps cutter load at low level.

## Spec

- Model number: 10R
- Size (mm): 146 x 17
- Weight (g): 100
- Rotation speed: 60000 min<sup>-1</sup>
- Exhaust system: rear
- Air pressure: 0.4 to 0.6 MPa
- Sound level: 75 dBA
- Chaking: 3mm
- Air connection port diameter: 2 minutes (1/4 inch)

## Product Catalog

Catalog Name	Page
ASTOOL Catalog 2021 > 2022 [Indirect Materials for Manufacturing]	61
ASTOOL Catalog 2018>2019 [Indirect Materials for Manufacturing]	69
AS ONE Catalog 2019 [Instruments for Laboratory]	295
AS ONE Catalog 2017 [Instruments for Laboratory]	253
ASTOOL Catalog 2016 > 2017 [Indirect Materials for Manufacturing]	76