

AXEL

3-5393-01 K Sheath Thermocouple (Stainless Steel (SUS316)) 650°C φ1.0 x 1000mm K-316-1.0-1000



Order No.	3-5393-01
Model No.	K-316-1.0-1000
JAN Code	0000000000000
	JPY: 10,600
	USD: 70.77
Standard price	
	Exchange rate 1USD= 149.78JPY Valid price in Japan
Quantity	1piece



Features

- It can measure high temperature furnace etc.
- It is bendable and can be aligned with measurements (* not repeated).

Spec

- Model number: K-316-1.0-1000
- Temperature range (°C): 0 - 650
- Sheath diameter x length (mm): φ1.0 x 1000
- Material: Sheath/stainless steel (SUS316), Lead wire/vinyl
- Lead wire length: 2m
- With omega connector

▶ Package size : 180×1300×10 mm 60 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	575
AS ONE Catalog 2021 [Instruments for Laboratory]	530
AS ONE Catalog 2019 [Instruments for Laboratory]	506
AS ONE Catalog 2017 [Instruments for Laboratory]	404