

# AXEL

NiGK Corporation

1-2854-01 Thermo Label R for Vacuum VL-40



Order No. 1-2854-01  
 Model No. VL-40  
 JAN Code 4582130423202

Standard price  
**JPY: 5,300**  
**USD: 35.42**

Exchange rate 1USD= 149.64JPY  
 Valid price in Japan

Quantity 1box(10sheets)



Cold

## Features

- Possible to see temperature under 1Pa ~ normal pressure at glance.
- It is adopted material of low outgassing type in order to reduce outgas from labels

## Spec

- Model number: VL-40
- Discoloration accuracy: +/- 2°C
- Size: Base/8 x 20mm, Thermochromic element/φ2mm
- Quantity: 1 box (10 sheets)
- Temperature combination: 40 - 45 - 50 - 55°C
- Primary color -> incident color: Light yellow -> black
- Irreversibility
- RoHS3 (EU)2015/863 Certificates can be issued

▶ Package size : 110×50×5 mm 10 g

## Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	610
AS ONE Catalog 2021 [Instruments for Laboratory]	569
AS ONE Catalog 2019 [Instruments for Laboratory]	545
AS ONE Catalog 2017 [Instruments for Laboratory]	429
AS ONE Catalog 2015 [Instruments for Laboratory]	394