



レジューサ (同心)

径の呼び (B) 大径×小径	外径 OD	FSGP		Sch40		Sch80		Sch120	
		内径 I D	厚さ T	内径 I D	厚さ T	内径 I D	厚さ T	内径 I D	厚さ T
1/2	21.7	16.1	2.8	16.1	2.8	14.3	3.7	—	—
3/4 × 1/2	27.2	21.6	2.8	21.4	2.9	19.4	3.9	—	—
1 × 3/4, 1/2	34.0	27.6	3.2	27.2	3.4	25.0	4.5	—	—
1 1/4 × 1, 3/4, 1/2	42.7	35.7	3.5	35.5	3.6	32.9	4.9	—	—
1 1/2 × 1 1/4, 1, 3/4, 1/2	48.6	41.6	3.5	41.2	3.7	38.4	5.1	—	—
2 × 1 1/2, 1 1/4, 1, 3/4	60.5	52.9	3.8	52.7	3.9	49.5	5.5	—	—
2 1/2 × 2, 1 1/2, 1 1/4, 1	76.3	67.9	4.2	65.9	5.2	62.3	7.0	—	—
3 × 2 1/2, 2, 1 1/2, 1 1/4	89.1	80.7	4.2	78.1	5.5	73.9	7.6	—	—
3 1/2 × 3, 2 1/2, 2, 1 1/2, 1 1/4	101.6	93.2	4.2	90.2	5.7	85.4	8.1	—	—
4 × 3 1/2, 3, 2 1/2, 2, 1 1/2	114.3	105.3	4.5	102.3	6.0	97.1	8.6	92.1	11.1
5 × 4, 3 1/2, 3, 2 1/2, 2	139.8	130.8	4.5	126.6	6.6	120.8	9.5	114.4	12.7
6 × 5, 4, 3 1/2, 3, 2 1/2	165.2	155.2	5.0	151.0	7.1	143.2	11.0	136.6	14.3
8 × 6, 5, 4, 3 1/2	216.3	204.7	5.8	199.9	8.2	190.9	12.7	179.9	18.2
10 × 8, 6, 5, 4	267.4	254.2	6.6	248.8	9.3	237.2	15.1	224.6	21.4
12 × 10, 8, 6, 5	318.5	304.7	6.9	297.9	10.3	283.7	17.4	267.7	25.4
14 × 12, 10, 8, 6	355.6	339.8	7.9	333.4	11.1	317.6	19.0	300.0	27.8
16 × 14, 12, 10, 8	406.4	390.6	7.9	381.0	12.7	363.6	21.4	344.6	30.9
18 × 16, 14, 12, 10	457.2	441.4	7.9	428.6	14.3	409.6	23.8	387.4	34.9
20 × 18, 16, 14, 12	508.0	492.2	7.9	477.8	15.1	455.6	26.2	431.8	38.1
22 × 20, 18, 16, 14	558.8	—	—	527.0	15.9	501.6	28.6	476.2	41.3
24 × 22, 20, 18, 16	609.6	—	—	574.6	17.5	547.6	31.0	517.6	46.0

注) 本表段落はFSGP, Sch40, Sch80の同心について作成してありますので
Sch120, Sch160, XXSおよび偏心の段落については別途御相談ください。

☆ 概略重量は基準寸法による計算値であり、炭素鋼の比重 7.85g/cm³ を使用しています。