

# コア継手の品揃え

[適用範囲] 流体：給水(上水、中水) / 温度：40℃以下 / 圧力：1MPa (10.2kgf/cm<sup>2</sup>)

※ ただし合F 5K 0.7MPa (7.1kgf/cm<sup>2</sup>) 合F 10K 1.0MPa (10.2kgf/cm<sup>2</sup>) となります

[適用管種] 水道用硬質塩化ビニルライニング鋼管：SGP-VA,VB  
水道用ポリエチレン粉体ライニング鋼管：SGP-PA,PB

**通常**  
タイプ

## ライニング鋼管接続用

品名	エルボ	45° エルボ	チー	ソケット	プラグ
呼び(B) 型番	L	45°L	T	S	P
1/2	●	●	●	●	●
3/4	●	●	●	●	●
1	●	●	●	●	●
1 1/4	●	●	●	●	●
1 1/2	●	●	●	●	●
2	●	●	●	●	●
2 1/2	●	●	●	●	●
3	●	●	●	●	●
4	●	●	●	●	●
5	●	●	●	●	●
6	●	●	●	●	●

品名	ユニオン	ニップル	クロス オーバー	合フランジ 合F	
呼び(B) 型番	U	Ni	OS	5KF	10KF
1/2	●	●			
3/4	●	●	●	●	●
1	●	●		●	●
1 1/4	●	●		●	●
1 1/2	●	●		●	●
2	●	●		●	●
2 1/2	●	●		●	●
3	●	●		●	●
4	●	●		●	●
5		●		●	●
6		●		●	●

品名	径違いエルボ	径違いチー	径違いソケット
呼び(B) 型番	RL	RT	RS
3/4	●	●	●
1	●	●	●
1 1/4	●	●	●
1 1/2	●	●	●
2	●	●	●
2 1/2	●	●	●
3	●	●	●
4	●	●	●
5	●	●	●
6	●	●	●



● プレシール品    ● プレシール未加工品