



FC-PF

FEMALE CONNECTOR PF

圧力計ユニオン (PF)



(METRIC)

TUBE O.D. T	THREADS PT or NPT	PART. No.	A	B	C	D	E	F	G	H
2	1/8	FC-2-1PF	28.5	12	11.9	9.5	1.3	14	8	24
2	1/4	FC-2-2PF	28.5	15	11.9	9.5	1.3	17	8	17
3	1/8	FC-3-1PF	33	12	16	15	2.5	14	12	26
3	1/4	FC-3-2PF	36	15	16	15	2.5	17	12	29
4	1/8	FC-4-1PF	35.3	12	18.3	15.3	3.5	14	14	28
4	1/4	FC-4-2PF	36.3	15	18.3	15.3	3.5	17	14	29
6	1/8	FC-6-1PF	35.4	12	18.4	15.4	5	14	14	28
6	1/4	FC-6-2PF	36.4	15	18.4	15.4	5	17	14	29
6	3/8	FC-6-3PF	38.4	16	18.4	15.4	5	22	14	31
6	1/2	FC-6-4PF	40.4	19	18.4	15.4	5	26	14	33
8	1/4	FC-8-2PF	36.8	15	18.8	16.8	6	17	15.87	29
8	3/8	FC-8-3PF	38.8	16	18.8	16.8	6	22	15.87	31
8	1/2	FC-8-4PF	40.8	19	18.8	16.8	6	26	15.87	33
10	1/4	FC-10-2PF	38.7	15	20.7	18.7	6	17	19	30
10	3/8	FC-10-3PF	40.7	16	20.7	18.7	6	22	19	32
10	1/2	FC-10-4PF	42.7	19	20.7	18.7	8	26	19	34
12	1/4	FC-12-2PF	40.8	15	22.8	22.8	6	22	23	30
12	3/8	FC-12-3PF	42.8	16	22.8	22.8	6	22	23	32
12	1/2	FC-12-4PF	44.8	19	22.8	22.8	10	26	23	34
14	3/8	FC-14-3PF	43.5	16	23.5	24.5	6	23	26	33
15	3/8	FC-15-3PF	43	16	23	24	6	23	26	33
16	1/2	FC-16-4PF	45.5	19	23.5	24.5	10	26	26	35
18	1/2	FC-18-4PF	47	19	24	25	10	27	30	36
20	1/2	FC-20-4PF	47	19	24	25	10	30	32	36
22	3/4	FC-22-6PF	50.2	21	25.2	25.2	18	35	35	39
25	1	FC-25-8PF	63	25	28.5	33.5	22	42	38	49

(INCHES)

※管外径5φも製作しております。

1/16" : 1.6	1/8	FC-005-1PF	28	12	11.4	9	1.3	14	8	24
1/16" : 1.6	1/4	FC-005-2PF	31	15	11.4	9	1.3	17	8	27
1/8" : 3.18	1/8	FC-01-1PF	33	10	16	15	2.5	14	12	26
1/8" : 3.18	1/4	FC-01-2PF	36	15	16	15	2.5	17	12	29
1/4" : 6.35	1/8	FC-02-1PF	35.4	12	18.4	15.4	5	14	14	28
1/4" : 6.35	1/4	FC-02-2PF	36.4	15	18.4	15.4	5	17	14	29
1/4" : 6.35	3/8	FC-02-3PF	38.4	16	18.4	15.4	5	22	14	31
1/4" : 6.35	1/2	FC-02-4PF	40.4	19	18.4	15.4	5	26	14	33
5/16" : 7.94	1/4	FC-025-2PF	36.8	15	18.8	16.8	6	17	15.87	29
5/16" : 7.94	3/8	FC-025-3PF	38.8	16	18.8	16.8	6	22	15.87	31
5/16" : 7.94	1/2	FC-025-4PF	40.8	19	18.8	16.8	6	26	15.87	33
3/8" : 9.53	1/4	FC-03-2PF	38.3	15	20.3	17.8	6	17	17.46	30
3/8" : 9.53	3/8	FC-03-3PF	40.3	16	20.3	17.8	6	22	17.46	32
3/8" : 9.53	1/2	FC-03-4PF	42.3	19	20.3	17.8	7	26	17.46	34
1/2" : 12.7	1/4	FC-04-2PF	40.8	15	22.8	22.8	6	22	23	30
1/2" : 12.7	3/8	FC-04-3PF	42.8	16	22.8	22.8	6	22	23	32
1/2" : 12.7	1/2	FC-04-4PF	44.8	19	22.8	22.8	10	26	23	34
5/8" : 15.87	3/8	FC-05-3PF	43.5	16	23.5	24.5	6	23	26	33
3/4" : 19.05	1/2	FC-06-4PF	47	19	24	25	10	27	30	36
7/8" : 22.23	3/4	FC-07-6PF	50.2	21	25.2	25.2	18	35	35	39
1" : 25.4	1	FC-08-8PF	63	25	28	33	22	42	38	49

(SCHEDULE)

※管外径3/16も製作しております。

1/8B : 10.5	1/8	FC-10.5-1PF	38.2	12	21.2	19.2	5	17	19	29
1/8B : 10.5	1/4	FC-10.5-2PF	39.2	15	21.2	19.2	6	17	19	30
1/8B : 10.5	3/8	FC-10.5-3PF	41.2	16	21.2	19.2	6	22	19	32
1/8B : 10.5	1/2	FC-10.5-4PF	43.2	19	21.2	19.2	8	26	19	34
1/4B : 13.8	1/4	FC-13.8-2PF	43	15	23	24	6	23	26	33
1/4B : 13.8	3/8	FC-13.8-3PF	43	16	23	24	6	23	26	33
1/4B : 13.8	1/2	FC-13.8-4PF	45	19	23	24	10	26	26	35
3/8B : 17.3	3/8	FC-17.3-3PF	47	16	24	25	6	27	30	36
3/8B : 17.3	1/2	FC-17.3-4PF	47	19	24	25	10	27	30	36
1/2B : 21.7	1/2	FC-21.7-4PF	49.2	19	25.2	25.2	10	30	35	38
1/2B : 21.7	3/4	FC-21.7-6PF	50.2	21	25.2	25.2	18	35	35	39

AIC,D:FINGER TIGHT±0.5mm (about)