



# RU

## REDUCING UNION

レジュアリングユニオン



### (METRIC)

(Unit:mm)

TUBE O.D.		PART. No.	A	C <sub>1</sub>	C <sub>2</sub>	D <sub>1</sub>	D <sub>2</sub>	E	G <sub>1</sub>	G <sub>2</sub>	F	H
T <sub>1</sub>	T <sub>2</sub>											
3	4	RU- 3• 4-0	41.3	16	18.3	15	15.3	2.5	12	14	14	27
4	6	RU- 4• 6-0	43.7	18.3	18.4	15.3	15.4	3.5	14	14	14	29
6	8	RU- 6• 8-0	44.2	18.4	18.8	15.4	16.8	5	14	15.87	14	29
6	10	RU- 6•10-0	46.1	18.4	20.7	15.4	18.7	5	14	19	17	30
8	10	RU- 8•10-0	46.5	18.8	20.7	16.8	18.7	6	15.87	19	17	30
8	12	RU- 8•12-0	48.6	18.8	22.8	16.8	22.8	6	15.87	23	22	30
10	12	RU-10•12-0	50.5	20.7	22.8	18.7	22.8	8	19	23	22	31
12	15	RU-12•15-0	52.8	22.8	23	22.8	24	10	23	26	23	32
15	18	RU-15•18-0	57	23	24	24	25	12	26	30	27	36
18	22	RU-18•22-0	59.2	24	25.2	25	25.2	15	30	35	30	37
22	25	RU-22•25-0	65.7	25.2	28.5	25.2	33.5	18	35	38	35	40

### (INCHES)

※管外径5φも製作しております。

1/8"	3.18	1/4"	6.35	RU-01•02-0	41.4	16	16.4	15	15.4	2.5	12	14	14	27
1/4"	6.35	3/8"	9.53	RU-02•03-0	45.7	18.4	20.3	15.4	17.8	5	14	17.46	17	30
1/4"	6.35	1/2"	12.7	RU-02•04-0	48.2	18.4	22.8	15.4	22.8	5	14	23	22	30
3/8"	9.53	1/2"	12.7	RU-03•04-0	50.1	20.3	22.8	17.8	22.8	7	17.46	23	22	31
1/2"	12.7	5/8"	15.87	RU-04•05-0	52.8	22.8	23	22.8	24	10	23	26	23	32
1/2"	12.7	3/4"	19.05	RU-04•06-0	56.8	22.8	24	22.8	25	10	23	30	27	35
3/4"	19.05	7/8"	22.23	RU-06•07-0	59.2	24	25.2	25.2	25.2	15	30	35	30	37
3/4"	19.05	1"	25.4	RU-06•08-0	64	25.2	28	25	33	15	30	38	35	39

### (SCHEDULE)

※管外径3/8φも製作しております。


1/8 B	10.5	1/4 B	13.8	RU-10.5•13.8-0	51.2	21.2	23	19.2	24	8	19	26	23	32
1/4 B	13.8	3/8 B	17.3	RU-13.8•17.3-0	57	23	24	24	25	12	26	30	27	36
3/8 B	17.3	1/2 B	21.7	RU-17.3•21.7-0	59.2	24	25.2	25	25.2	15	30	35	30	37

A.C.D.:FINGER TIGHT-±0.5mm (about)

# UC

## UNION CROSS

クロスユニオン



TUBE O.D.	PART. No.	A	D	E	G	H
4	UC- 4-0	59	16	3.5	14	42
6	UC- 6-0	58	15.4	5	14	42
8	UC- 8-0	61.5	16.8	6	15.87	44.5
10	UC-10-0	75.5	18.7	8	19	58
12	UC-12-0	79	22.8	10	23	58
14	UC-14-0	79	24.5	12	26	58
15	UC-15-0	78	24	12	26	58
16	UC-16-0	79	24.5	12	26	58


※管外径5φも製作しております。

6.35	UC-02-0	42	15.4	5	14	58
9.53	UC-03-0	46.5	17.8	7	17.46	64.5
12.7	UC-04-0	79	22.8	10	23	58
15.87	UC-05-0	78	24	12	26	58

※管外径3/8φも製作しております。

10.5	UC-10.5-0	76.5	19.2	8	19	58
13.8	UC-13.8-0	78	24	12	26	58

※管外径10mm以上の製品は熔断切りになります。



ステンレスチューブ・クランプ