



3.5MPa B1型銅管くい込継手  
(35kgf/cm<sup>2</sup>)

**GL-1型**

**B1 UNION ELBOW**





呼称 Designation of Joints	P	E	h	H	B	A
4 -B1	4	2.5	8	10	16	25
6 -B1	6	4	8	12	19	27
8 -B1	8	6	10	14	19	27
10-B1	10	8	12	17	20	29
12-B1	12	10	14	19	22	32
14-B1	14	11	17	23	25	34
15-B1	15	12	17	23	25	34
20-B1	20	17	23	29	29	39
25-B1	25	20	29	36	35	45

3.5MPa B1型銅管くい込継手  
(35kgf/cm<sup>2</sup>)

**GSP-B1型**

**FEMAL CONNECTOR FOR PRESSURE GAUGE**



呼称 Designation of Joints	P	G (PF)	E	E <sub>1</sub>	h	H	l <sub>1</sub>	l <sub>1</sub>	L
GSP 1/4 × 6 -B1	6	1/4	4	6	17	12	29	14	37
GSP 1/4 × 8 -B1	8	1/4	6	6	17	14	29	14	37
GSP 1/4 × 10-B1	10	1/4	8	6	17	17	29	14	38
GSP 3/8 × 6 -B1	6	3/8	4	6	21	12	30	15	38
GSP 3/8 × 8 -B1	8	3/8	6	6	21	14	30	15	38
GSP 3/8 × 10-B1	10	3/8	8	8	21	17	30	15	39
GSP 1/2 × 6 -B1	6	1/2	4	6	26	12	33	16	40
GSP 1/2 × 8 -B1	8	1/2	6	6	26	14	33	16	40
GSP 1/2 × 10-B1	10	1/2	8	8	26	17	33	16	41