


JIS B 2316-SCH80 (※印除く)

単位：mm


No.1 12SS フルカップリング



呼び方	B	D	E	C	L	O
SWFC-8A-S80	14.3	9.4	6.4	10	26.4	22
SWFC-10A-S80	17.8	12.7	6.4	10	26.4	26
SWFC-15A-S80	22.2	16.1	9.5	10	29.5	32
SWFC-20A-S80	27.7	21.4	9.5	13	35.5	38
SWFC-25A-S80	34.5	27.2	12.7	13	38.7	46
SWFC-32A-S80	43.2	35.5	12.7	13	38.7	55
SWFC-40A-S80	49.1	41.2	12.7	13	38.7	65
SWFC-50A-S80	61.1	52.7	19.1	16	51.1	75

単位：mm


No.1 17SS ハーフカップリング



呼び方	B	D	F	C	L	O
SWHC-8A-S80	14.3	9.4	15.9	10	25.9	22
SWHC-10A-S80	17.8	12.7	17.5	10	27.5	26
SWHC-15A-S80	22.2	16.1	22.2	10	32.2	32
SWHC-20A-S80	27.7	21.4	23.8	13	36.8	38
SWHC-25A-S80	34.5	27.2	28.6	13	41.6	46
SWHC-32A-S80	43.2	35.5	30.2	13	43.2	55
SWHC-40A-S80	49.1	41.2	31.8	13	44.8	65
SWHC-50A-S80	61.1	52.7	41.3	16	57.3	75

単位：mm


※No.139SS ボス



呼び方	B	D	F	C	L	O
SWBOSS-8A-S80	14.3	9.4	15.9	10	25.9	22
SWBOSS-10A-S80	17.8	12.7	17.5	10	27.5	26
SWBOSS-15A-S80	22.2	16.1	22.2	10	32.2	32
SWBOSS-20A-S80	27.7	21.4	23.8	13	36.8	38
SWBOSS-25A-S80	34.5	27.2	28.6	13	41.6	46
SWBOSS-32A-S80	43.2	35.5	30.2	13	43.2	55
SWBOSS-40A-S80	49.1	41.2	31.8	13	44.8	65
SWBOSS-50A-S80	61.1	52.7	41.3	16	57.3	75

単位：mm

※No.1 19SS オリング式ユニオン FAS



呼び方	B	D	E	C	L	O	H	リング
SWOU-8A	14.3	9.4	22	10	42	22	36	P16
SWOU-10A	17.8	12.7	22	10	42	26	41	P20
SWOU-15A	22.2	16.1	22	10	42	32	46	G25
SWOU-20A	27.7	21.4	30	13	56	38	55	G30
SWOU-25A	34.5	27.2	30	13	56	46	八角65	G35
SWOU-32A	43.2	35.5	30	14	58	55	八角77	G45
SWOU-40A	49.1	41.2	42	16	74	63	八角85	G50
SWOU-50A	61.1	52.7	42	16	74	75	八角100	G65