

# High Performance Rework Station & Accessories

## Optional Tips for the FM-2032

Unit: mm

<b>T30-D06 Shape-0.6D</b> 	<b>T30-D1 Shape-1D</b> 	<b>T30-I Shape-I</b> 	<b>T30-J Shape-J</b> 	<b>T30-KU Shape-KU</b> 	<b>T30-KN Shape-KN</b> 
-------------------------------	----------------------------	--------------------------	--------------------------	----------------------------	----------------------------

## Optional Tips for the FM-2022

Unit: mm

### CHIP

\*1 set: 2 pcs

<b>T8-1001 Chip 0.5L</b> 	<b>T8-1002 Chip 0.5C</b> 	<b>T8-1003 Chip 1L</b> 	<b>T8-1004 Chip 2L</b> 	<b>T8-1013 Chip 3L</b> 
------------------------------	------------------------------	----------------------------	----------------------------	----------------------------

### SOP

<b>T8-1005 SOP 6L</b> 	<b>T8-1006 SOP 8L</b> 	<b>T8-1007 SOP 10L</b> 	<b>T8-1008 SOP 13L</b> 	<b>T8-1009 SOP 16L</b> 
<b>T8-1010 SOP 20L</b> 	<b>T8-1011 SOP 25L</b> 	<b>T8-1012 SOP 18L</b> 		

## Replacement Tips for the FM-2023

Unit: mm

### CHIP

\*1 set: 2 pcs

<b>T9-I Chip I</b> 	<b>T9-L1 Chip 1L</b> 	<b>T9-L2 Chip 2L</b> 
------------------------	--------------------------	--------------------------

## Optional Tips for the FM-2030

Unit: mm

<b>T22-BL Shape-BL</b> 	<b>T22-BL2 Shape-2BL</b> 	<b>T22-BC2 Shape-2BC</b> 	<b>T22-C3 Shape-3C</b> 	<b>T22-C5 Shape-5C</b> 	<b>T22-C6 Shape-6C</b> 
<b>T22-D08 Shape-0.8D</b> 	<b>T22-D12 Shape-1.2D</b> 	<b>T22-D16 Shape-1.6D</b> 	<b>T22-D24 Shape-2.4D</b> 	<b>T22-D32 Shape-3.2D</b> 	<b>T22-D45 Shape-4.5D</b> 
<b>T22-D52 Shape-5.2D</b> 	<b>T22-J02 Shape-0.2J</b> 	<b>T22-JD08 Shape-0.8JD</b> 	<b>T22-K Shape-K</b> 		