

# A/AF

●アルミ ナベ小ネジ、サラ小ネジ (十字穴付) ●Aluminum screws ●铝 螺丝 (十字)

RoHS対応製品

仕様

- ナベ小ネジ ・材質/アルミ  
・処理/生地
- ナイロンワッシャー ・材質/ナイロン66  
・色 /半透明  
・熱変形温度/1.82MPa...75℃  
・UL規格/UL94V-2(材料)

- PTFEワッシャー ・材質/PTFE  
・色 /白色不透明  
・耐熱温度/連続240℃不燃性  
・UL規格/UL94V-0(材料)



A-0000ナベ小ネジ				A-0000-Nセットナベ小ネジ(KW付)				A-0000-Tセットナベ小ネジ(KW付)				AF-0000サラ小ネジ			
ねじ径	ピッチ-D	H	L	品番	KW ナイロン d-t	L	品番	KW PTFE d-t	L	品番	ピッチ-D	L	品番		
M2.6	0.45-4.5-1.7		4	A-2604	5.5-0.8	4	A-2604-N	5.5-0.8	4	A-2604-T	0.5-6				
			5	A-2605		5	A-2605-N		5	A-2605-T					
			6	A-2606		6	A-2606-N		6	A-2606-T					
			8	A-2608		8	A-2608-N		8	A-2608-T					
			10	A-2610		10	A-2610-N		10	A-2610-T					
			12	A-2612		12	A-2612-N		12	A-2612-T					
M3	0.5-5.5-2.0		6	A-0306	6-0.8	6	A-0306-N	8-0.8	6	A-0306-T	6	AF-0306			
			8	A-0308		8	A-0308-N		8	A-0308-T	8	AF-0308			
			10	A-0310		10	A-0310-N		10	A-0310-T	10	AF-0310			
			12	A-0312		12	A-0312-N		12	A-0312-T	12	AF-0312			
			15	A-0315		15	A-0315-N		15	A-0315-T					
			16	A-0316		16	A-0316-N		16	A-0316-T					
M4	0.7-7-2.6		6	A-0406	10-1.0	6	A-0406-N	10-1.0	6	A-0406-T	0.7-8	6	AF-0406		
			8	A-0408		8	A-0408-N		8	A-0408-T		8	AF-0408		
			10	A-0410		10	A-0410-N		10	A-0410-T		10	AF-0410		
			12	A-0412		12	A-0412-N		12	A-0412-T		12	AF-0412		
			15	A-0415		15	A-0415-N		15	A-0415-T		15	AF-0415		
			16	A-0416		16	A-0416-N		16	A-0416-T		16	AF-0416		
M5	0.8-9-3.3		6	A-0506	12-1.0	6	A-0506-N	12-1.0	6	A-0506-T	0.8-10	8	AF-0508		
			8	A-0508		8	A-0508-N		8	A-0508-T		10	AF-0510		
			10	A-0510		10	A-0510-N		10	A-0510-T		12	AF-0512		
			12	A-0512		12	A-0512-N		12	A-0512-T		15	AF-0515		
			15	A-0515		15	A-0515-N		15	A-0515-T		16	AF-0516		
			16	A-0516		16	A-0516-N		16	A-0516-T		20	AF-0520		
M6	1.0-10.5-3.9		20	A-0520		20	A-0520-N		20	A-0520-T	1.0-12	25	AF-0525		
			25	A-0525		25	A-0525-N		25	A-0525-T		30	AF-0530		
			30	A-0530		30	A-0530-N		30	A-0530-T					
			8	A-0608										12	AF-0612
			10	A-0610										15	AF-0615
			12	A-0612										16	AF-0616
M6	1.0-10.5-3.9		15	A-0615							20	AF-0620			
			16	A-0616							25	AF-0625			
			20	A-0620							30	AF-0630			
			25	A-0625											
			30	A-0630											