



E寸法は最終ページHose径寸法参照

Part No.		A (Hose O.D)	T	E1	h (HEX)	H (HEX)	\varnothing	$\varnothing 1$	L	(D)
ANSI NPT	ISO/JIS R	mm	NPT/R	mm	mm	mm	mm	mm	mm	mm
EPCT 4.76X□-2 ss	EPCT 4.76X□-R2 ss	4.76	1/8	4.8	12	12	27.5	6.0	26.5	1.5
EPCT 4.76X□-4 ss	EPCT 4.76X□-R4 ss	4.76	1/4	7.1	14	12	31.5	6.0	30.5	1.5
EPCT 6.35X□-2 ss	EPCT 6.35X□-R2 ss	6.35	1/8	4.8	14	14	27.3	6.8	26.5	2.0
EPCT 6.35X□-4 ss	EPCT 6.35X□-R4 ss	6.35	1/4	7.1	14	14	32.3	6.8	31.5	2.0
EPCT 6.35X□-6 ss	EPCT 6.35X□-R6 ss	6.35	3/8	9.0	19	14	33.0	6.8	32.2	2.0
	EPCT 6.35X□-R6 ss	6.35	3/8	9.0	19	14	34.0	6.8	33.2	2.0
EPCT 9.53X□-2 ss	EPCT 9.53X□-R2 ss	9.53	1/8	4.8	17	17	30.0	8.0	29.5	2.0
EPCT 9.53X□-4 ss	EPCT 9.53X□-R4 ss	9.53	1/4	7.1	17	17	34.0	8.0	33.5	2.0
EPCT 9.53X□-6 ss	EPCT 9.53X□-R6 ss	9.53	3/8	9.0	19	17	35.0	8.0	34.5	2.0
	EPCT 9.53X□-R6 ss	9.53	3/8	9.0	19	17	36.0	8.0	35.5	2.0
EPCT 9.53X□-8 ss	EPCT 9.53X□-R8 ss	9.53	1/2	12.7	22	17	40.0	8.0	39.5	2.0
EPCT 12.7X□-4 ss	EPCT 12.7X□-R4 ss	12.7	1/4	7.1	22	22	38.0	9.0	37.5	2.0
EPCT 12.7X□-6 ss	EPCT 12.7X□-R6 ss	12.7	3/8	9.0	22	22	39.0	9.0	38.5	2.0
EPCT 12.7X□-8 ss	EPCT 12.7X□-R8 ss	12.7	1/2	12.7	22	22	42.7	9.0	42.2	2.0
EPCT 12.7X□-12 ss	EPCT 12.7X□-R12 ss	12.7	3/4	18.3	27	22	44.5	9.0	44.0	2.0
	EPCT 12.7X□-R12 ss	12.7	3/4	18.3	27	22	44.5	9.0	50.0	2.0
EPCT 19.05X□-6 ss	EPCT 19.05X□-R6 ss	19.05	3/8	9.0	27	27	45.0	11.0	43.0	2.0
	EPCT 19.05X□-R6 ss	19.05	3/8	9.0	27	27	46.0	11.0	44.0	2.0
EPCT 19.05X□-8 ss	EPCT 19.05X□-R8 ss	19.05	1/2	12.7	27	27	50.0	11.0	48.0	2.0
EPCT 19.05X□-12 ss	EPCT 19.05X□-R12 ss	19.05	3/4	18.3	27	27	52.0	11.0	50.0	2.0
	EPCT 19.05X□-R16 ss	19.05	1	22.5	36	27	56.5	11.0	54.5	2.0