



H : See dimensional data(Last page)

Part No.		A(Tube O. D)		T	E	h(Flat)		l	L	L ₁	F
ANSI NPT	ISO/JIS Rc	in	mm	NPT/Rc	mm	in	mm	mm	mm	mm	mm
DTH 2-2	DTH 2-R2	1/8	3.18	1/8	2.3	5/8	15.9	17.5	24.2	19.0	13.0
DTH 2-4	DTH 2-R4	1/8	3.18	1/4	2.3	13/16	20.6	20.5	27.2	22.5	13.0
	DTH 2-R6	1/8	3.18	3/8	2.3	13/16	20.6	26.2	32.9	22.5	13.0
DTH 4-2	DTH 4-R2	1/4	6.35	1/8	4.8	5/8	15.9	19.0	26.5	19.0	15.4
DTH 4-4	DTH 4-R4	1/4	6.35	1/4	4.8	13/16	20.6	22.5	30.0	22.5	15.4
	DTH 4-R6	1/4	6.35	3/8	4.8	15/16	23.8	24.7	32.2	22.5	15.4
	DTH 4-R8	1/4	6.35	1/2	4.8	1-1/16	27.0	28.2	35.7	28.5	15.4
	DTH 5-R4	5/16	7.94	1/4	6.4	13/16	20.6	23.1	30.6	22.5	16.3
DTH 6-2	DTH 6-R2	3/8	9.53	1/8	7.1	5/8	15.9	23.0	30.5	19.0	17.0
DTH 6-4	DTH 6-R4	3/8	9.53	1/4	7.1	13/16	20.6	24.0	31.5	22.5	17.0
DTH 6-6	DTH 6-R6	3/8	9.53	3/8	7.1	15/16	23.8	26.2	33.7	22.5	17.0
	DTH 6-R8	3/8	9.53	1/2	7.1	1-1/16	27.0	28.2	36.0	28.5	17.0
DTH 8-4	DTH 8-R2	1/2	12.7	1/8	10.4	13/16	20.6	25.0	35.3	22.5	23.0
	DTH 8-R4	1/2	12.7	1/4	10.4	13/16	20.6	25.0	35.3	22.5	23.0
DTH 8-6	DTH 8-R6	1/2	12.7	3/8	10.4	15/16	23.8	26.2	36.5	22.5	23.0
DTH 8-8	DTH 8-R8	1/2	12.7	1/2	10.4	1-1/16	27.0	28.2	38.8	28.5	23.0
	DTH 8-R12	1/2	12.7	3/4	10.4	1-5/16	33.3	31.8	42.1	31.8	23.0
DTH10-6	DTH10-R2	5/8	15.88	1/8	12.7	15/16	23.8	27.0	37.3	22.5	24.6
	DTH10-R6	5/8	15.88	3/8	12.7	15/16	23.8	27.0	37.3	22.5	24.6
	DTH10-R8	5/8	15.88	1/2	12.7	1-1/16	27.0	28.2	38.5	28.5	24.6
	DTH12-R2	3/4	19.05	1/8	15.8	1-1/16	27.0	28.2	38.5	28.5	24.6
	DTH12-R4	3/4	19.05	1/4	15.8	1-1/16	27.0	28.2	38.5	28.5	24.6
	DTH12-R6	3/4	19.05	3/8	15.8	1-1/16	27.0	28.2	38.5	28.5	24.6
DTH12-8	DTH12-R8	3/4	19.05	1/2	15.8	1-1/16	27.0	28.2	38.5	28.5	24.6
DTH12-12	DTH12-R12	3/4	19.05	3/4	15.8	1-5/16	33.3	31.8	42.1	31.8	24.6
DTH14-12		7/8	22.23	3/4	18.3	1-5/16	33.3	32.5	42.7	31.8	31.6
DTH16-16	DTH16-R12	1	25.4	3/4	22.5	1-5/16	33.3	33.3	45.9	31.8	31.6
	DTH16-R16	1	25.4	1	22.5	1-7/8	47.6	38.6	51.2	38.1	31.6