



H : See dimensional data(Last page)

Part No.	A (Tube O. D)		B (Pipe size)		E	E ₁	h (HEX)		L	l	l ₁	F
	in	mm	Nom.	mm			in	mm				
DCB 2-2	1/8	3.18	1/8	10.3	2.3	5.5	7/16	11.11	29.8	23.1	9.7	13.0
DCB 3-2	3/16	4.76	1/8	10.3	3.0	5.5	7/16	11.11	31.1	24.4	9.7	13.8
DCB 4-2	1/4	6.35	1/8	10.3	4.8	5.5	1/2	12.7	33.2	25.7	9.7	15.4
DCB 4-4	1/4	6.35	1/4	13.7	4.8	7.7	9/16	14.29	37.8	30.3	14.2	15.4
DCB 4-6	1/4	6.35	3/8	17.0	4.8	10.4	11/16	17.46	38.7	31.2	14.2	15.4
DCB 4-8	1/4	6.35	1/2	21.3	4.8	13.9	7/8	22.23	44.2	36.7	19.1	15.4
DCB 6-4	3/8	9.53	1/4	13.7	7.1	7.7	5/8	15.88	40.0	32.5	14.2	17.0
DCB 6-6	3/8	9.53	3/8	17.0	7.1	10.4	11/16	17.46	40.0	32.5	14.2	17.0
DCB 6-8	3/8	9.53	1/2	21.3	7.1	13.9	7/8	22.23	45.6	38.1	19.1	17.0
DCB 8-4	1/2	12.7	1/4	13.7	10.4	7.7	13/16	20.64	43.6	33.3	14.2	23.0
DCB 8-6	1/2	12.7	3/8	17.0	10.4	10.4	13/16	20.64	43.6	33.3	14.2	23.0
DCB 8-8	1/2	12.7	1/2	21.3	10.4	13.9	7/8	22.23	48.4	38.1	19.1	23.0
DCB 8-12	1/2	12.7	3/4	26.5	10.4	18.8	1-1/16	26.99	50.9	40.6	19.1	23.0
DCB 10-8	5/8	15.88	1/2	21.3	12.7	13.9	15/16	23.81	49.2	38.9	19.1	24.6
DCB 12-6	3/4	19.05	3/8	17.0	15.8	10.4	1-1/16	26.99	45.9	35.6	14.2	24.6
DCB 12-8	3/4	19.05	1/2	21.3	15.8	13.9	1-1/16	26.99	50.8	40.5	19.1	24.6
DCB 12-12	3/4	19.05	3/4	26.5	15.8	18.8	1-1/16	26.99	50.9	40.6	19.1	24.6
DCB 12-16	3/4	19.05	1	33.4	15.8	24.3	1-3/8	34.93	57.9	47.6	23.9	24.6
DCB 16-8	1	25.4	1/2	21.3	22.5	13.9	1-3/8	34.93	57.6	45.0	19.1	31.6
DCB 16-16	1	25.4	1	33.4	22.5	24.3	1-3/8	34.93	62.6	50.0	23.9	31.6