



Part No.	A	B (Pipe size)		E	E ₁	h	H	l	l ₁	L	F
	mm	in	mm	mm	mm	HEX	HEX	mm	mm	mm	mm
MDCB 3M-2	3	1/8	10.3	2.4	5.5	12	12	23.9	9.7	30.6	13.0
MDCB 4M-2	4	1/8	10.3	2.7	5.5	12	13	24.6	9.7	31.4	13.9
MDCB 6M-2	6	1/8	10.3	4.8	5.5	14	14	26.5	9.7	34.0	15.4
MDCB 6M-4	6	1/4	13.7	4.8	7.7	14	14	31.0	14.2	38.5	15.4
MDCB 6M-6	6	3/8	17.1	4.8	10.7	19	14	33.0	14.2	40.5	15.4
MDCB 6M-8	6	1/2	21.3	4.8	13.9	22	14	37.4	19.1	44.9	15.4
MDCB 8M-2	8	1/8	10.3	6.4	5.5	17	17	26.7	9.7	34.2	16.3
MDCB 8M-4	8	1/4	13.7	6.4	7.7	17	17	33.3	14.2	40.8	16.3
MDCB 8M-6	8	3/8	17.1	6.4	10.7	19	17	33.3	14.2	40.8	16.3
MDCB 8M-8	8	1/2	21.3	6.4	13.9	22	17	38.1	19.1	45.6	16.3
MDCB 10M-4	10	1/4	13.7	7.9	7.7	19	19	33.3	14.2	41.1	17.3
MDCB 10M-6	10	3/8	17.1	7.9	10.7	19	19	33.3	14.2	41.1	17.3
MDCB 10M-8	10	1/2	21.3	7.9	13.9	22	19	39.0	19.1	46.8	17.3
MDCB 12M-4	12	1/4	13.7	9.5	7.7	22	22	33.3	14.2	43.5	22.9
MDCB 12M-6	12	3/8	17.1	9.5	10.7	22	22	34.1	14.2	44.3	22.9
MDCB 12M-8	12	1/2	21.3	9.5	13.9	22	22	39.0	19.1	49.2	22.9
MDCB 15M-8	15	1/2	21.3	12.0	13.9	24	27	38.7	19.1	48.7	24.3
MDCB 15M-12	15	3/4	26.7	12.0	18.8	27	27	41.4	19.1	51.4	24.3
MDCB 16M-8	16	1/2	21.3	12.7	13.9	24	27	39.7	19.1	49.9	24.5
MDCB 16M-12	16	3/4	26.7	12.7	18.8	27	27	41.4	19.1	51.6	24.5
MDCB 18M-8	18	1/2	21.3	15.1	13.9	27	30	41.0	19.1	51.2	24.5
MDCB 18M-12	18	3/4	26.7	15.1	18.8	27	30	42.7	19.1	52.9	24.5
MDCB 20M-12	20	3/4	26.7	16.5	18.8	30	30	41.4	19.1	51.6	24.5
MDCB 25M-12	25	3/4	26.7	22.5	18.8	36	41	46.2	19.1	58.7	31.6
MDCB 25M-16	25	1	33.4	22.5	24.3	36	41	51.0	23.9	63.5	31.6