



IKO Stroke Rotary Bushing **Open Type**

	Ordinary type								Heavy load type							
Shape	ST								ST...B							
																
Size	4	5	6	8	10	12	16	—	—	—	8	10	12	16		
	20	25	30	35	40	45	50	20	25	30	35	40	45	50		
	55	60	70	80	90	100		55	60	70	80	90	100			

Shaft diameter mm	Identification number					Nominal dimensions mm				
	Ordinary type		Mass (Ref.) g	Heavy load type		Mass (Ref.) g	F_w	D	L_1	L_2
4	ST	4814	2.9	—		—	4	8	14	9
5	ST	51016	5.6	—		—	5	10	16	10.6
6	ST	61219	8.9	—		—	6	12	19	13.2
8	ST	81524	15.6	ST	81524 B	16.8	8	15	24	17.1
10	ST	101930	28.8	ST	101930 B	31.2	10	19	30	22.7
12	ST	122332	42	ST	122332 B	46	12	23	32	24.5
16	ST	162837	71	ST	162837 B	75	16	28	37	29.1
20	ST	203245	99	ST	203245 B	106	20	32	45	35.8
25	ST	253745	117	ST	253745 B	125	25	37	45	35.8
30	ST	304565	205	ST	304565 B	220	30	45	65	53.5
35	ST	355270	329	ST	355270 B	346	35	52	70	58.5
40	ST	406080	516	ST	406080 B	540	40	60	80	68.3
45	ST	456580	563	ST	456580 B	588	45	65	80	68.3
50	ST	5072100	827	ST	5072100 B	862	50	72	100	86.4
55	ST	5580100	1 160	ST	5580100 B	1 200	55	80	100	86.4
60	ST	6085100	1 240	ST	6085100 B	1 290	60	85	100	86.4
70	ST	7095100	1 400	ST	7095100 B	1 450	70	95	100	86.4
80	ST	80110100	2 050	ST	80110100 B	2 110	80	110	100	86
90	ST	90120100	2 250	ST	90120100 B	2 330	90	120	100	86
100	ST	100130100	2 440	ST	100130100 B	2 520	100	130	100	86