

## ■標準タイプ

| 品番           | 適用 注)<br>位置決め穴径 | D <sub>4</sub> | D <sub>3</sub> | H <sub>4</sub> | S    | H    | H <sub>1</sub> | D <sub>2</sub><br>(g6) | H <sub>2</sub> | D  |
|--------------|-----------------|----------------|----------------|----------------|------|------|----------------|------------------------|----------------|----|
| CP710-04015A | φ 3.8~φ 5.2     | 3.1            | 6              | 7.6            | 7.4  | 20.6 | 13             | 15                     | 7.5            | 35 |
| CP710-05015A | φ 4.8~φ 6.2     | 4.1            | 7              |                |      |      |                |                        |                |    |
| CP710-06020A | φ 5.8~φ 8.2     | 5.1            | 9              | 9.6            | 9.9  | 27.6 | 18             | 20                     | 10             | 40 |
| CP710-08020A | φ 7.8~φ 10.2    | 7.1            | 11             |                |      |      |                |                        |                |    |
| CP710-10025A | φ 9.3~φ 12.7    | 8.6            | 13.5           | 11.6           | 12.4 | 34.6 | 23             | 25                     | 12.5           | 45 |
| CP710-12025A | φ 12.3~φ 15.7   | 11.6           | 16.5           |                |      |      |                |                        |                |    |

| 品番           | D <sub>1</sub> | W  | H <sub>3</sub> | d   | P  | 持上力<br>(N) | 質量<br>(g) | 価格     |
|--------------|----------------|----|----------------|-----|----|------------|-----------|--------|
| CP710-04015A | 15             | 16 | 6              | 4.5 | 25 | 6.4~19.3   | 45        | 9,400  |
| CP710-05015A |                |    |                |     |    |            |           | 9,400  |
| CP710-06020A | 20             | 22 | 8              |     | 30 | 5.5~20.5   | 95        | 9,900  |
| CP710-08020A |                |    |                |     |    |            |           | 9,900  |
| CP710-10025A | 25             | 26 | 10             |     | 35 | 8.5~19.8   | 160       | 11,000 |
| CP710-12025A |                |    |                |     |    |            |           | 170    |

## ■サポータータイプ

| 品番           | 適用 注)<br>位置決め穴径 | D <sub>4</sub> | D <sub>3</sub> | H <sub>4</sub> | S    | H    | H <sub>1</sub><br>(±0.01) | D <sub>2</sub><br>(g6) | H <sub>2</sub> | D  |
|--------------|-----------------|----------------|----------------|----------------|------|------|---------------------------|------------------------|----------------|----|
| CP710-04015B | φ 3.8~φ 5.2     | 3.1            | 6              | 5.6            | 7.4  | 20.6 | 15                        | 15                     | 7.5            | 35 |
| CP710-05015B | φ 4.8~φ 6.2     | 4.1            | 7              |                |      |      |                           |                        |                |    |
| CP710-06020B | φ 5.8~φ 8.2     | 5.1            | 9              | 7.6            | 9.9  | 27.6 | 20                        | 20                     | 10             | 40 |
| CP710-08020B | φ 7.8~φ 10.2    | 7.1            | 11             |                |      |      |                           |                        |                |    |
| CP710-10025B | φ 9.3~φ 12.7    | 8.6            | 13.5           | 9.6            | 12.4 | 34.6 | 25                        | 25                     | 12.5           | 45 |
| CP710-12025B | φ 12 ~φ 16      | 11.6           | 16.5           |                |      |      |                           |                        |                |    |

| 品番           | D <sub>1</sub> | W  | H <sub>3</sub> | d   | P  | 持上力<br>(N) | 質量<br>(g) | 価格     |
|--------------|----------------|----|----------------|-----|----|------------|-----------|--------|
| CP710-04015B | 15             | 16 | 6              | 4.5 | 25 | 6.4~19.3   | 50        | 9,700  |
| CP710-05015B |                |    |                |     |    |            |           | 9,700  |
| CP710-06020B | 20             | 22 | 8              |     | 30 | 5.5~20.5   | 100       | 11,000 |
| CP710-08020B |                |    |                |     |    |            |           | 11,000 |
| CP710-10025B | 25             | 26 | 10             |     | 35 | 8.5~19.8   | 170       | 12,000 |
| CP710-12025B |                |    |                |     |    |            |           | 12,000 |

注)適用穴径の範囲内では、ワーク側の位置決め穴の面取りは、最大C1まで対応できます。