



| Hub | Insert | Cap | Handle | Arm |
|--|-------------------------------------|----------------------------------|--|--|
| Glass-fiber reinforced polyamide plastic Glossy Finish Black | Steel(SUM22L) Black oxide finish | Aluminum(A1080P) Silver matte | Phenolic plastic Glossy Finish Black | Steel(SUM22L) Chrome plated Silver matte |

| Part Number | A | B | C | D | E | F | G (H7) | H | J | K | M | N | P | R | Weight (g) |
|-------------|----|----|-----|----|----|----|-----------|----|---|-----|----|-----|------|----|---------------|
| CL37 | 37 | 46 | 81 | 20 | 18 | 17 | 8 | 26 | 5 | 25° | 21 | 4.3 | 13.8 | 10 | 75 |
| CL45 | 45 | 52 | 108 | 25 | 22 | 22 | | 32 | 6 | 20° | 25 | 7.0 | 17.5 | | 132 |
| CL54 | 54 | 61 | 127 | 30 | 26 | 27 | 10 | 39 | 8 | | 31 | 7.3 | 20.2 | 12 | 213 |

- Removable cap.
- Adaptable for click positioning applications with use of a ball and a spring [CLB](#) (sold separately)
- Use in hot or highly humid circumstances can deteriorate the plastic material properties.
- Working temperature : Between -20°C and 110°C