

ES1N,ES2N,ES3N,ES4N


SCALE PLATES




Type	Body
ES1N ES2N	Aluminum (A1050P) Graduations etched
ES1N-SUS ES2N-SUS	Stainless steel (SUS304) Graduations etched
ES3N ES4N	Aluminum (A1050P) Graduations etched

Single Side


ES1N ES1N-SUS : Mounting-Hole Marks
ES2N ES2N-SUS : 3.5-dia. Through Holes




- ES1N -U50R,100R,150R,200R
- ES1N-SUS -U50R,100R
- ES2N -U50R,100R,150R,200R,500R
- ES2N-SUS -U50R,100R




- ES1N -U50L,100L,150L,200L
- ES1N-SUS -U50L,100L
- ES2N -U50L,100L,150L,200L,500L
- ES2N-SUS -U50L,100L




- ES1N -U5050,100100
- ES1N-SUS -U5050
- ES2N -U5050,100100,250250
- ES2N-SUS -U5050




- ES1N -D50R,100R,150R,200R
- ES2N -D50R,100R,150R,200R,500R



- ES1N -D50L,100L,150L,200L
- ES2N -D50L,100L,150L,200L,500L




- ES1N -D5050,100100
- ES2N -D5050,100100,250250




Both Sides

Mounting Hole Spacing for 500mm-long Scale Plates


ES3N : Mounting-Hole Marks
ES4N : 3.5-dia. Through Holes



- ES3N -50U,100U
- ES4N -50U,100U



- ES3N -50D,100D
- ES4N -50D,100D



- ES3N -5050
- ES4N -5050