



B 形 1 本掛										B 形 2 本掛											
W=24 (mm)										W=44 (mm)											
呼び	外径 (d.e)	dm	軸穴 最大径	軸穴 下径	形状 図番	Db	L	S ₁	S ₂	重量 (kg)	呼び	外径 (d.e)	dm	軸穴 最大径	軸穴 下径	形状 図番	Db	L	S ₁	S ₂	質量 (kg)
2	50.8	39.8	12	9	①の1	35	40	16		0.3	2	50.8	39.8	12	9	①の1	35	60	16		0.5
2½	63.5	52.5	22		"	41	43	19		0.6	2½	63.5	52.5	22		"	41	63	19		0.8
3	76.2	65.2	25		②の1	45	28	19	15	0.7	3	76.2	65.2	28		④の1		28		16	1.0
3½	88.9	77.9	"		"	"	"	"	"	0.8	3½	88.9	77.9	30		④の1		28		16	1.3
4	101.6	90.6	28		"	"	"	"	"	1.0	4	101.6	90.6	28		②の1	50	32	19	31	1.4
4½	114.3	103.3	"		"	"	"	"	"	1.2	4½	114.3	103.3	40		④の1		28		16	1.8
5	127.0	116.0	32		"	"	"	"	"	1.4	5	127.0	116.0	50	12	④の1		28		16	2.1
5½	139.7	128.7	"		"	"	"	"	"	1.6	5½	139.7	128.7	32		②の1	57	32	19	31	2.5
6	152.4	141.4	28		②の2	50	30	11	5	1.6	6	152.4	141.4	35		⑤の2	64	38	3	3	2.6
6½	165.1	154.1	"	12	"	"	"	"	"	1.6	6½	165.1	154.1	"	"	"	"	"	"	"	2.9
7	177.8	166.8	32		"	"	"	"	"	1.9	7	177.8	166.8	"	"	"	"	"	"	"	3.1
8	203.2	192.2	"		"	"	"	"	"	2.1	8	203.2	192.2	"	"	"	"	"	"	"	3.4
9	228.6	217.6	"		"	"	"	"	"	2.4	9	228.6	217.6	42		"	76	43	0.5	0.5	5.0
10	254.0	243.0	35		"	"	"	"	"	2.8	10	254.0	243.0	"	"	"	"	"	"	"	5.0
11	279.4	268.4	"		①の2	"	"	9		3.2	11	279.4	268.4	"	15	"	"	"	"	"	5.3
12	304.8	293.8	"		"	"	"	"		3.4	12	304.8	293.8	45		"	82	"	"	"	5.9
13	330.2	319.2	"		"	"	"	"		4.0	13	330.2	319.2	"	"	"	"	"	"	"	6.3
14	355.6	344.6	"		"	"	"	"		4.4	14	355.6	344.6	"	"	"	"	"	"	"	7.1
15	381.0	370.0	"		"	"	"	"		4.8	15	381.0	370.0	"	"	"	"	"	"	"	7.9
16	406.4	395.4	38		"	"	"	"		5.2	16	406.4	395.4	50		"	88	"	"	"	8.4
											18	457.2	446.2	"	"	"	"	"	"	"	10.7
											20	508.0	497.0	"	22	"	"	"	"	"	12.5
											22	558.8	547.8	"	"	"	"	"	"	"	12.7
											24	609.6	598.6	"	"	"	"	"	"	"	14.2