



C形3本掛										C形4本掛												
W=84 (mm)										W=110 (mm)												
呼び	外径 (d.e)	dm	軸穴d		形状 図番	Db	L	S <sub>1</sub>	S <sub>2</sub>	質量 (kg)	呼び	外径 (d.e)	dm	軸穴d		形状 図番	Db	L	S <sub>1</sub>	S <sub>2</sub>	質量 (kg)	
			最大径	下径										最大径	下径							
4	101.6	87.6	30	18	⑤の1	50	13	21	2.9	4	101.6	87.6	30	18	⑤の1	58	15	37	3.5			
4½	114.3	100.3	40	"	"	"	"	"	3.6	4½	114.3	100.3	40	"	"	"	"	"	"	"	4.5	
5	127.0	113.0	50	"	"	"	"	"	4.6	5	127.0	113.0	50	"	"	"	"	"	"	"	5.6	
5½	139.7	125.7	55	"	"	"	"	"	5.5	5½	139.7	125.7	55	"	"	"	"	"	"	"	6.75	
6	152.4	138.4	60	20	"	"	"	"	6.1	6	152.4	138.4	60	20	"	"	"	"	"	"	8.2	
6½	165.1	151.1	65	"	"	"	"	"	7.9	6½	165.1	151.1	65	"	"	"	"	"	"	"	9.3	
7	177.8	163.8	70	"	"	"	"	"	9.2	7	177.8	163.8	70	"	"	"	"	"	"	"	11.3	
8	203.2	189.2	50	"	⑤の2	89	62	11	11	8.6	8	203.2	189.2	50	"	⑤の2	92	74	18	18	11.0	
9	228.6	214.6	"	"	"	92	"	"	"	9.8	9	228.6	214.6	55	22	"	95	"	"	"	12.4	
10	254.0	240.0	"	"	⑤の3	"	"	"	"	11.1	10	254.0	240.0	"	"	"	"	"	"	"	13.1	
11	279.4	265.4	55	22	"	95	"	"	"	11.6	11	279.4	265.4	56	"	⑤の3	100	"	"	"	14.7	
12	304.8	290.8	"	"	"	"	"	"	"	12.4	12	304.8	290.8	"	"	"	"	"	"	"	15.6	
13	330.2	316.2	"	25	"	98	"	"	"	13.5	13	330.2	316.2	"	25	"	"	"	"	"	16.9	
14	355.6	341.6	"	"	"	100	"	"	"	14.4	14	355.6	341.6	"	"	"	"	"	"	"	17.8	
15	381.0	367.0	"	"	"	"	"	"	"	15.7	15	381.0	367.0	60	"	"	107	"	"	"	20.2	
16	406.4	392.4	"	"	"	"	"	"	"	17.6	16	406.4	392.4	"	"	"	"	"	"	"	22.1	
18	457.2	443.2	"	"	"	"	"	"	"	19.8	18	457.2	443.2	"	"	"	"	"	"	"	26.3	
20	508.0	494.0	"	"	"	"	68	8	8	24.4	20	508.0	494.0	63	30	"	114	82	14	14	30.5	
22	558.8	544.8	63	30	"	114	"	"	"	27.3	22	558.8	544.8	"	"	"	"	"	"	"	33.1	
24	609.6	595.6	"	"	"	"	74	5	5	29.5	24	609.6	595.6	"	"	"	"	"	"	"	35.8	
26	660.4	646.4	"	"	"	"	"	"	"	33.6	26	660.4	646.4	67	"	"	120	88	11	11	40.5	
28	711.2	697.2	65	"	"	120	"	"	"	36.5	28	711.2	697.2	"	"	"	"	"	"	"	44.0	
30	762.0	748.0	"	"	"	"	"	"	"	38.4	30	762.0	748.0	71	"	"	127	"	"	"	49.2	

(注) 当サイズについては、お問い合わせ下さい。