

一般・給水・給湯配管用継手品種と寸法表

ねじ込み式管継手 JIS規格品

品種 略号 呼び(B)	エルボ	45°エルボ	ストリート エルボ	チー	サービス チー	クロス	キャップ	ソケット	フランジ	ロック ナット	プラグ	ユニオン	ニップル	バンド
	L	45°L	SL	T	ST	CR	CA	S	F	LN	P	U	NI	BE
1/8	●		●	●				●			●		●	
1/4	●	●	●	●		●	●	●		●	●	●	●	●
3/8	●	●	●	●		●	●	●		●	●	●	●	●
1/2	●	●	●	●	●	●	●	●		●	●	●	●	●
3/4	●	●	●	●	●	●	●	●		●	●	●	●	●
1	●	●	●	●	●	●	●	●		●	●	●	●	●
1 1/4	●	●	●	●	●	●	●	●		●	●	●	●	●
1 1/2	●	●	●	●	●	●	●	●		●	●	●	●	●
2	●	●	●	●	●	●	●	●		●	●	●	●	●
2 1/2	●	●	●	●	●	●	●	●		●	●	●	●	●
3	●	●	●	●	●	●	●	●		●	●	●	●	●
4	●	●	●	●	●	●	●	●		●	●	●	●	●
5	●	●	●	●	●	●	●	●		●	●	●	●	●
6	●	●	●	●	●	●	●	●		●	●	●	●	●

品種 略号 呼び(B)	径違い エルボ	径違い チー	径違い ソケット	プッシング
	RL	RT	RS	BU
1/4×1/8	●		●	●
3/8×1/8	●			●
3/8×1/4	●	●	●	●
1/2×1/8				●
1/2×1/4	●	●	●	●
1/2×3/8	●	●	●	●
3/4×1/8				●
3/4×1/4	●	●	●	●
3/4×3/8	●	●	●	●
3/4×1/2	●	●	●	●
1×1/4				●
1×3/8	●	●	●	●
1×1/2	●	●	●	●
1×3/4	●	●	●	●
1 1/4×1/4				●
1 1/4×3/8				●
1 1/4×1/2	●	●	●	●

品種 略号 呼び(B)	径違い エルボ	径違い チー	径違い ソケット	プッシング
	RL	RT	RS	BU
1 1/4×3/4	●	●	●	●
1 1/4×1	●	●	●	●
1 1/2×1/4				●
1 1/2×3/8	●	●	●	●
1 1/2×1/2	●	●	●	●
1 1/2×3/4	●	●	●	●
1 1/2×1	●	●	●	●
1 1/2×1 1/4	●	●	●	●
2×3/8				●
2×1/2	●	●	●	●
2×3/4	●	●	●	●
2×1	●	●	●	●
2×1 1/4	●	●	●	●
2×1 1/2	●	●	●	●
2 1/2×1/2	●	●	●	●
2 1/2×3/4	●	●	●	●
2 1/2×1	●	●	●	●

品種 略号 呼び(B)	径違い エルボ	径違い チー	径違い ソケット	プッシング
	RL	RT	RS	BU
2 1/2×1 1/4	●	●	●	●
2 1/2×1 1/2	●	●	●	●
2 1/2×2	●	●	●	●
3×1/2				●
3×3/4				●
3×1	●	●	●	●
3×1 1/4	●	●	●	●
3×1 1/2	●	●	●	●
3×2	●	●	●	●
3×2 1/2	●	●	●	●
4×1/2		●	●	●
4×3/4		●	●	●
4×1		●	●	●
4×1 1/4	●	●	●	●
4×1 1/2	●	●	●	●
4×2	●	●	●	●
4×2 1/2	●	●	●	●

品種 略号 呼び(B)	径違い エルボ	径違い チー	径違い ソケット	プッシング
	RL	RT	RS	BU
4×3	●	●	●	●
5×1		●		
5×1 1/4		●		
5×1 1/2		●	●	●
5×2		●	●	●
5×2 1/2		●	●	●
5×3	●	●	●	●
5×4	●	●	●	●
6×1		●		
6×1 1/4		●		
6×1 1/2		●		
6×2		●	●	●
6×2 1/2		●	●	●
6×3	●	●	●	●
6×4	●	●	●	●
6×5	●	●	●	●

■一部の商品は、JIS規格品ではありませんが、JIS規格に準拠しております。(詳しくは当社管継手カタログをご参照下さい。)

パイプニップル JIS規格準拠品

(パレルニップル)

(ロングニップル)

呼び(B)	長さmm	
1/8	24	●
1/4	26	●
3/8	28	●
1/2	34	●
3/4	38	●
1	42	●
1 1/4	50	●
1 1/2	50	●
2	58	●
2 1/2	70	●
3	78	●
4	90	●
5	103	●
6	103	●

呼び(B) 長さmm	1/8	1/4	3/8	1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4	5	6
	50mm	●	●	●	●	●	●							
65mm	●	●	●	●	●	●	●	●						
75mm	●*	●	●	●	●	●	●	●						
90mm	●*	●*	●	●	●	●	●	●						
100mm	●	●	●	●	●	●	●	●	●	●				
115mm	●*	●*	●*	●*	●	●	●	●						
125mm	●	●	●	●	●	●	●	●	●	●	●	●	●	●
140mm	●*	●*	●*	●*	●	●	●*	●*	●					
150mm	●	●	●	●	●	●	●	●	●	●	●	●	●	●
175mm		●	●	●	●	●	●	●*	●	●*	●*			
200mm		●	●	●	●	●	●	●	●	●	●	●	●	●
250mm		●	●	●	●	●	●	●	●	●	●	●	●	●
300mm		●	●	●	●	●	●	●	●	●	●	●	●	●

*印の黒パイプニップルは受注生産品です。