



PIN-BUTTON 6-LOBE BOLT

ピン・ボタン 6-ロブボルト

	#6-32	#10-24	#10-32	1/4-20	5/16-18
dk	6.7	9.2	9.2	11	14
k	1.9	2.6	2.6	3.4	4.3
ドライバーサイズ	T10	T25	T25	T27	T40

インチねじ

サイズ	製品コード				梱包
	d	L	ステンレス A2	ステン黒染め ナイロック加工	
#6-32	3/8		TX01.00632.030	TX0100632030BK TX0100632030NY	100
	1/2		TX01.00632.040	TX0100632040BK TX0100632040NY	100
	3/4		TX01.00632.060	TX0100632060BK TX0100632060NY	100
	1		TX01.00632.100	TX0100632100BK TX0100632100NY	100
#10-24	1/2		TX01.01024.040	TX0101024040BK TX0101024040NY	100
	1		TX01.01024.100	TX0101024100BK TX0101024100NY	100
	1-1/4		TX01.01024.120	TX0101024120BK TX0101024120NY	100
	1-1/2		TX01.01024.140	TX0101024140BK TX0101024140NY	100
#10-32	1/2		TX01.01032.040	TX0101032040BK TX0101032040NY	100
	3/4		TX01.01032.060	TX0101032060BK TX0101032060NY	100
	1-1/4		TX01.01032.120	TX0101032120BK TX0101032120NY	100
	1-1/2		TX01.01032.140	TX0101032140BK TX0101032140NY	100
1/4-20	3/4		TX01.02020.060	TX0102020060BK TX0102020060NY	100
	1		TX01.02020.100	TX0102020100BK TX0102020100NY	100
	1-1/4		TX01.02020.120	TX0102020120BK TX0102020120NY	100
	1-1/2		TX01.02020.140	TX0102020140BK TX0102020140NY	100
5/16-18	3/4		TX01.02518.060	TX0102518060BK TX0102518060NY	100
	1		TX01.02518.100	TX0102518100BK TX0102518100NY	100
	1-1/2		TX01.02518.140	TX0102518140BK TX0102518140NY	100

1本から出荷致します！詳しくはお問い合わせください。
製品コード末尾「BK」=黒染め、「NY」=ナイロック加工。

戻り止めネジ

Nylok® ナイロック®

- 強力な戻り止め機能
- 繰り返し使える
- ガンリン・油・グリス・溶剤にも負けない
- 軽くて錆びない
- 作業性が抜群

EL



BK



HE



TX



SP



OW



TW



SF



PH



TC



NR



TOOLS

Order
Made