

BNC-R-F Single Ended Floating Shield

Coaxial-floating



Dimensions in inches (mm)

NW / KF Flange

No. of Pins	INSTALLATION	A	B	C	D	REFERENCE	PART NUMBER
1	NW / KF 16	1.18 (30)	.24 (6)	.42 (10.8)	1.30 (33)	N16BRF1	11045
1	NW / KF 25	1.57 (40)	.24 (6)	.72 (18.3)	1.00 (25.5)	N25BRF1	11069
1	NW / KF 40	2.16 (55)	.24 (6)	.72 (18.3)	1.00 (25.5)	N40BRF1	10309
2	NW / KF 40	2.16 (55)	.24 (6)	.72 (18.3)	1.00 (25.5)	N40BRF2	11114
3	NW / KF 40	2.16 (55)	.24 (6)	.72 (18.3)	1.00 (25.5)	N40BRF3	10308

ConFlat® Flange

No. of Pins	INSTALLATION	A	B	C	D	REFERENCE	PART NUMBER
1	CF 1.33	1.33 (34)	.30 (7.5)	.28 (7.2)	1.44 (36.6)	C34BRF1	10025
1	CF 2.75	2.75 (70)	.50 (12.7)	.74 (18.8)	.98 (25)	C70BRF1	10234
2	CF 2.75	2.75 (70)	.50 (12.7)	.74 (18.8)	.98 (25)	C70BRF2	10240
3	CF 2.75	2.75 (70)	.50 (12.7)	.74 (18.8)	.98 (25)	C70BRF3	10318

Accessories

Description	REFERENCE	PART NUMBER
.094 Socket Contact Set Screw Vacuum Side	SVC24S	10152
BNC Air Side Plug	ASP-BNC	10017

For more details, see Section 6.1

- Introduction
- Table of Contents
- Glance
- Coaxial**
- Multipin
- Thermocouple
- High Voltage & High Current
- Isolator
- Accessories
- Custom-made products
- Technical Data
- Part number & Reference Index
- Custom-made Application Sheet
- Trademarks