



Dimensions in inches (mm)

NW / KF Flange

No. of Pins	INSTALLATION	A	B	D	REFERENCE	PART NUMBER
9	NW / KF 40	2.16 (55)	.24 (6)	.96 (24.5)	N40MD91	11581
15	NW / KF 50	2.96 (75)	.24 (6)	.96 (24.5)	N50MD151	11582

ConFlat® Flange

No. of Pins	INSTALLATION	A	B	D	REFERENCE	PART NUMBER
9	CF 2.75	2.75 (70)	.50 (12.7)	.95 (24)	C70MD91	11566
15	CF 4.50	4.50 (114)	.69 (17.5)	.95 (24)	C114MD151	11567
25	CF 4.50	4.50 (114)	.69 (17.5)	.95 (24)	C114MD251	11568

ISO-K Flange

No. of Pins	INSTALLATION	A	B	D	REFERENCE	PART NUMBER
25	ISO - K 63	3.74 (95)	.472 (12)	.87 (22)	I63MD251	12320

Accessories

Description	REFERENCE	PART NUMBER
Kapton® Cable Assembly with Socket Contacts in Type-D In-Vacuum PEEK® Insulator	VCA500MD9P/X	12161
	VCA1000MD9P/X	12163
	VCA500MD15P/X	12165
	VCA1000MD15P/X	12167
	VCA500MD25P/X	12270
	VCA1000MD25P/X	12271
	VCA500MD9D/X	12169
	VCA1000MD9D/X	12171
	VCA500MD15D/X	12173
	VCA1000MD15D/X	12175
Teflon® Cable Assembly with Socket Contacts in Type-D In-Vacuum Stainless Steel/DTC Insulator	VCA500MD25D/X	12272
	VCA1000MD25D/X	12273
	ASP9D	11816
Air Side Plug	ASP15D	11831
	ASP25D	11931
.04 Socket Contact Vacuum Side	SVC10	10499

For more details, see Section 6.2

Introduction
Table of Contents
Glance
Coaxial
Multipin
Thermocouple
High Voltage & High Current
Isolator
Accessories
Custom-made products
Technical Data
Part number & Reference Index
Custom-made Application Sheet
Trademarks