



Dimensions in inches (mm)

NW / KF Flange

No. of Pins	INSTALLATION	A	B	C	D	P.C.D.	REFERENCE	PART NUMBER
1	NW / KF 16	1.18 (30)	.24 (6)	2.19 (55.5)	1.75 (44.5)	— (—)	N25K3A1SUS	11517
2	NW / KF 16	1.18 (30)	.24 (6)	1.89 (48)	2.05 (52)	.32 (8)	N25K3A2SUS	11518
4	NW / KF 16	1.18 (30)	.24 (6)	1.89 (48)	2.05 (52)	.40 (10)	N25K3A4SUS	11519
1	NW / KF 25	1.57 (40)	.24 (6)	2.19 (55.5)	1.75 (44.5)	— (—)	N35K3A1SUS	11100
2	NW / KF 25	1.57 (40)	.24 (6)	2.19 (55.5)	1.75 (44.5)	.32 (8)	N35K3A2SUS	11101
4	NW / KF 25	1.57 (40)	.24 (6)	2.19 (55.5)	1.75 (44.5)	.40 (10)	N35K3A4SUS	11102

ConFlat® Flange

No. of Pins	INSTALLATION	A	B	C	D	P.C.D.	REFERENCE	PART NUMBER
1	CF 1.33	1.33 (34)	.30 (7.5)	2.21 (56)	1.73 (44)	— (—)	C15K3A1SUS	10602
2	CF 1.33	1.33 (34)	.30 (7.5)	1.77 (44.8)	2.17 (55.2)	.32 (8)	C15K3A2SUS	10213
4	CF 1.33	1.33 (34)	.30 (7.5)	1.77 (44.8)	2.17 (55.2)	.40 (10)	C15K3A4SUS	10212
1	CF 2.75	2.75 (70)	.50 (12.7)	2.21 (56)	1.73 (44)	— (—)	C25K3A1SUS	11256
2	CF 2.75	2.75 (70)	.50 (12.7)	2.21 (56)	1.73 (44)	.32 (8)	C25K3A2SUS	11257
4	CF 2.75	2.75 (70)	.50 (12.7)	2.21 (56)	1.73 (44)	.40 (10)	C25K3A4SUS	11258

Accessories

Description	REFERENCE	PART NUMBER
.05 Socket Contact Vacuum Side	SVC15	10146

For more details, see Section 6.4

Introduction
Table of Contents
Glance
Coaxial
Multipin
Thermocouple
High Voltage & High Current
Isolator
Accessories
Custom-made products
Technical Data
Part number & Reference Index
Custom-made Application Sheet
Trademarks