



Dimensions in inches (mm)

**NW / KF Flange**

No. of Pins	INSTALLATION	A	B	C	D	P.C.D.	REFERENCE	PART NUMBER
1	NW / KF 16	1.18 (30)	.24 (6)	4.58 (116.5)	2.90 (73.5)	- (-)	N25K110A1CUM5	10103
1	NW / KF 25	1.57 (40)	.24 (6)	4.58 (116.5)	2.90 (73.5)	- (-)	N35K110A1CUM5	10303
2	NW / KF 25	1.57 (40)	.24 (6)	4.58 (116.5)	2.90 (73.5)	.55 (14)	N35K110A2CUM5	10421
1	NW / KF 40	2.16 (55)	.24 (6)	4.58 (116.5)	2.90 (73.5)	- (-)	N45K110A1CUM5	10294
2	NW / KF 40	2.16 (55)	.24 (6)	4.58 (116.5)	2.90 (73.5)	.87 (22)	N45K110A2CUM5	10131
3	NW / KF 40	2.16 (55)	.24 (6)	4.58 (116.5)	2.90 (73.5)	.91 (23)	N45K110A3CUM5	10270
4	NW / KF 40	2.16 (55)	.24 (6)	4.58 (116.5)	2.90 (73.5)	1.02 (26)	N45K110A4CUM5	10302

**ConFlat® Flange**

No. of Pins	INSTALLATION	A	B	C	D	P.C.D.	REFERENCE	PART NUMBER
1	CF 1.33	1.33 (34)	.30 (7.5)	4.61 (117)	2.87 (73)	- (-)	C15K110A1CUM5	10432
1	CF 2.75	2.75 (70)	.50 (12.7)	4.61 (117)	2.87 (73)	- (-)	C25K110A1CUM5	10020
2	CF 2.75	2.75 (70)	.50 (12.7)	4.61 (117)	2.87 (73)	.87 (22)	C25K110A2CUM5	10021
3	CF 2.75	2.75 (70)	.50 (12.7)	4.61 (117)	2.87 (73)	.91 (23)	C25K110A3CUM5	10450
4	CF 2.75	2.75 (70)	.50 (12.7)	4.61 (117)	2.87 (73)	.91 (23)	C25K110A4CUM5	10022

**Accessories**

Description	REFERENCE	PART NUMBER
.25 Socket Contact Vacuum Side	SVC64	10155

For more details, see Section 6.4

Introduction  
Table of Contents  
Glance  
Coaxial  
Multipin  
Thermocouple  
High Voltage & High Current  
Isolator  
Accessories  
Custom-made products  
Technical Data  
Part number & Reference Index  
Custom-made Application Sheet  
Trademarks