

● SUS304-TS Straight 293



Tube size	Thread size					
	M5×0.8	M6×1	R1/8	R1/4	R3/8	R1/2
4	M5	M6	01	02	—	—
6	M5	M6	01	02	03	—
8	—	—	01	02	03	—
10	—	—	01	02	03	04
12	—	—	—	02	03	04
16	—	—	—	—	03	04

● SUS304-US Union straight 293



Tube size
4
6
8
10
12
16

● SUS304-USD Different diameter union 293



Tube size
6-4
8-6
10-8
12-10
16-12

● SUS304-TL Elbow 294



Tube size	Thread size					
	M5×0.8	M6×1	R1/8	R1/4	R3/8	R1/2
4	M5	M6	01	02	—	—
6	M5	M6	01	02	03	—
8	—	—	01	02	03	—
10	—	—	01	02	03	04
12	—	—	—	02	03	04
16	—	—	—	—	03	04

● SUS304-UL Union elbow 294



Tube size
4
6
8
10
12
16

● SUS304-TT Tee 295



Tube size	Thread size					
	M5×0.8	M6×1	R1/8	R1/4	R3/8	R1/2
4	M5	M6	01	02	—	—
6	M5	M6	01	02	03	—
8	—	—	01	02	03	—
10	—	—	01	02	03	04
12	—	—	—	02	03	04
16	—	—	—	—	03	04

● SUS304-TB Branch tee 296



Tube size	Thread size					
	M5×0.8	M6×1	R1/8	R1/4	R3/8	R1/2
4	M5	M6	01	02	—	—
6	M5	M6	01	02	03	—
8	—	—	01	02	03	—
10	—	—	01	02	03	04
12	—	—	—	02	03	04
16	—	—	—	—	03	04

● SUS304-UT Union tee 296



Tube size
4
6
8
10
12
16

● SUS304-UTD Different diameter union tee 297



Tube size
6-4
8-6
10-8
12-10

● SUS304-TBY Branch Y 297



Tube size	Thread size					
	M5×0.8	M6×1	R1/8	R1/4	R3/8	R1/2
4	M5	M6	01	02	—	—
6	M5	M6	01	02	03	—
8	—	—	01	02	03	—
10	—	—	01	02	03	04
12	—	—	—	02	03	04