

**DEEP GROOVE BALL BEARINGS
SERIES 6800**

KSK Bearing Number	Bore d		Out.Dia. D		Width B		Approx. Net Weight (Kg)	(Interchange)			
	mm	inches	mm	inches	mm	inches		ADR	SKF(Eur.)	FAG	ELGES
6800	10.000	0.3937	19.000	0.7480	5.000	0.1969	0.008	X-10	61800	61800T	61800
6801	12.000	0.4724	21.000	0.8268	5.000	0.1969	0.009	61801	61801	61801T	61801
6802	15.000	0.5906	24.000	0.9449	5.000	0.1969	0.009	61802	61802	61802T	61802
6803	17.000	0.6693	26.000	1.0236	5.000	0.1969	0.009	61803	61803	61803T	61803
6804	20.000	0.7874	32.000	1.2598	7.000	0.2756	0.018		61804	61804T	61804-Y
6805	25.000	0.9843	37.000	1.4567	7.000	0.2756	0.023		61805	61805T	61805-Y
6806	30.000	1.1811	42.000	1.6535	7.000	0.2756	0.027		61806	61806T	61806-Y
6807	35.000	1.3780	47.000	1.8504	7.000	0.2756	0.030		61807	61807T	61807-Y
6808	40.000	1.5748	52.000	2.0472	7.000	0.2756	0.035		61808	61808T	61808-Y
6809	45.000	1.7717	58.000	2.2835	7.000	0.2756	0.040		61809	61809T	61809-Y

Note:

- (1) Also available double shielded (ZZ) and double sealed (2RS). No change in width dimensions.
- (2) C3 and C4 radial clearances are available on all of the above sizes.
- (3) Also available in ABEC 3 and 5 precision. Consult for availability.