



Magic Tube

Ro Product in compliance with RoHS Directive

Passed Railway Vehicle Materials Fire Test (Certified level: Fire-retardant)

AAA

- The magic fasteners permit the tube to be fit and released quickly without using a tool.
- Available in 8 sizes from 15φ to 100φ, the tube ensures ideal insulation for different wiring needs.
- Quick and easy to fit and release, the tube makes it easy to change or check the wiring.
- The material is so flexible that it can fit any shape and help produce a neat appearance.
- Partially detachable, the tube permits the branching of wiring.
- The reversible type (black and gray) flexibly meets application purposes.
- The reversible type (black and gray) flexibly satisfies inventory needs, contributing a lot to inventory reduction.

Color

- Reversible type (black & gray)
- Gray

Packaging and Packaging Unit

- Every 25m of a tube is packed in a compact cardboard case. When using the tube, you can just pull the required length out of the slot of the case.

Designation Format

- Reversible type (R):
KMT-N(Nominal Size)R
Example: Nominal size of 20φ > KMT-N20R
- Gray type (G):
KMT-N(Nominal Size)G
Example: Nominal size of 20φ > KST-N20G

Part No.	Nominal Size	Length	Materials/Characteristics
KMT-N15	15φ	25m	· Sheet section: Fire-resistant vinyl chloride with polyester fabric · Interlock section: Hook-and-loop fasteners Width of hook and loop fasteners 15φ-20φ: 12mm 25φ-100φ: 16mm
KMT-N20	20φ		
KMT-N25	25φ		
KMT-N30	30φ		
KMT-N40	40φ		
KMT-N50	50φ		
KMT-N70	70φ		
KMT-N100	100φ		

Sheet portion: Equivalent to VTM-O specification complied product

Electric-Materials



Slide Lock Tube

Ro Product in compliance with RoHS Directive

Passed Railway Vehicle Materials Fire Test (Certified level: Fire-retardant)

Features

- Extra workability is ensured by the material of the interlock section that changes its hardness little even at a low temperature.
- The interlock section provides excellent air-tightness to prevent the inclusion of external dust.
- Available in 10 sizes from 10φ to 100φ, the tube ensures ideal insulation for different wiring needs.
- The material is so flexible that it can fit any shape and help produce a neat appearance.

How to Interlock

- The tube can be interlocked easily using the exclusive slider (optional).

Color

- Black
- Gray

Packaging

- The external case has a slot from which you can pull the tube out to use.
- Not using any metallic parts, the bobbin and the external case can be readily disposed of.

Designation Format

- Black type:
KSL-(Nominal Size)
Example: Nominal size of 10φ > KSL-10
- Gray type:
KSL-(Nominal Size)G
Example: Nominal size of 25φ > KSL-25G



Exclusive slider (optional)

Part No.	Nominal Size	Length	Materials/Characteristics
KSL-10	10φ	50m	· Sheet section: Fire-resistant vinyl chloride with polyester fabric · Interlock section: Fire-resistant semi-rigid vinyl chloride
KSL-15	15φ		
KSL-20	20φ		
KSL-25	25φ		
KSL-30	30φ		
KSL-35	35φ		
KSL-40	40φ		
KSL-50	50φ		
KSL-70	70φ	25m	
KSL-100	100φ		

Sheet section: VTM-O