



UNITRONIC® LiYCY A

Screened data transmission cable with colour code acc. to DIN 47100 UL/CSA recognized

Info

- A for Advanced here: UL and CSA certifications



Benefits

- Overall braid minimises electrical interference

Application range

- Wiring of devices, machines and plants intended for export to the North American market or countries where UL-/CSA certified cables are used.
- For the North American market

Product features

- Flame-retardant acc. to IEC 60332-1-2, UL VW-1 & CSA FT 1

Norm references / Approvals

- UL AWM Style 2464
- CSA AWM I/II A
- UL File No. E63634

Product Make-up

- Multi-wire strand made of tinned copper wires
- Core insulation made of PVC
- Tinned-copper braiding
- Outer sheath made of special PVC compound
Outer sheath colour: dark grey (RAL 7005)

Technical data

- Classification**
ETIM 5.0 Class-ID: EC000830
ETIM 5.0 Class-Description: Data cable
- Core identification code**
DIN 47100 without colour repetition, refer to Appendix T9
- Peak operating voltage**
(not for power applications)
300 V
UL/CSA: 300 V
- Conductor stranding**
AWG conductor sizes, 7 or 19 wires
- Minimum bending radius**
Occasional flexing: 15 x outer diameter
Fixed installation: 6 x outer diameter
- Test voltage**
1500 V
- Temperature range**
Occasional flexing: -5°C to +70°C
Fixed installation: -40°C to +80°C

Article number	Number of cores and AWG per conductor	Number of cores and mm ² per conductor	Outer diameter (mm)	Copper index (kg/km)	Weight (kg/km)
UNITRONIC® LiYCY A					
0044602	2 x AWG26/7	2 x 0.14	4.3	15.6	29.5
0044604	4 x AWG26/7	4 x 0.14	4.7	18	33
0044652	2 x AWG24/7	2 x 0.23	4.7	17.6	36.1
0044655	5 x AWG24/7	5 x 0.23	5.5	28.5	51
0044658	8 x AWG24/7	8 x 0.23	6.4	31.1	72.2
0044662	12 x AWG24/7	12 x 0.23	7.3	51.8	96
0044702	2 x AWG22/7	2 x 0.34	5.5	17.6	32
0044703	3 x AWG22/7	3 x 0.34	5.7	21.2	36
0044704	4 x AWG22/7	4 x 0.34	6.1	27.3	44
0044705	5 x AWG22/7	5 x 0.34	6.6	30.8	53
0044707	7 x AWG22/7	7 x 0.34	7.1	46.4	71
0044712	12 x AWG22/7	12 x 0.34	8.9	66.8	120
0044716	16 x AWG22/7	16 x 0.34	9.8	83.9	145
0044721	21 x AWG22/7	21 x 0.34	11.3	109.4	170
0044732	2 x AWG20/7	2 x 0.50	6	24.4	41
0044733	3 x AWG20/7	3 x 0.50	6.3	29.9	47
0044735	5 x AWG20/7	5 x 0.50	7.3	49.2	72
0044738	8 x AWG20/7	8 x 0.50	8.5	70.8	102
0044850	7 x AWG18/19	7 x 1.00	8.9	93.2	160.8
0044851	10 x AWG18/19	10 x 1.00	11.5	130.9	200

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.
Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.
Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths
Packaging size: Coil 152 m; Drum 305 m
Photographs are not to scale and do not represent detailed images of the respective products.

Similar products

- UNITRONIC® LiYCY (TP) A refer to page 302

Accessories

- SKINTOP® MS-SC-M refer to page 732
- KS 15 cable shears
- DATA STRIP stripping tool refer to page 1001