



SILVYN® FPAG PG / SILVYN® FPAG 90° PG



SILVYN® FPAG PG



SILVYN® FPAG 90° PG

Benefits

SILVYN® FPAG PG

- Fast assembly
- High-tensile
- Sealing
- Vibration protection

SILVYN® FPAG 90° PG

- 90° elbow allows easy installation
- Fast assembly
- High-tensile
- Sealing
- Vibration protection

Application range

- In combination with protective conduit:
- SILVYN® FPAS
- Applications with strong vibrations

Product features

- In black colour UV-resistant and weather-proofed
- Removeable with a screwdriver

Norm references / Approvals

- UL FILENUMBER E308201

Product Make-up

SILVYN® FPAG PG

- PG connection thread
- Body
- Upper part with integrated all-round toothing

SILVYN® FPAG 90° PG

- PG connection thread
- 90° elbow
- Body
- Upper part with integrated all-round toothing

Suitable conduits

- SILVYN® FPAS Page 875

Technical data

	ETIM 5.0 Class-ID: EC001178 ETIM 5.0 Class-Description: Screw connection for protective plastic hose
	Certifications IEC EN 61386-23
	On request SILVYN® FPAG PG IP68 version
	Colour delivered Grey (RAL 7031) Black (RAL 9005), UV-resistant
	Material PA66 Halogen-free
	Protection rating IP 66
	Temperature range -50°C to +135°C

Article number	PG size	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAG PG black			
55506585	7	10	10
55506595	9/1	10	10
55506605	9/2	13	10
55506615	9/3	16	10
55506625	11	16	10
55506635	13,5/1	16	10
55506645	13,5/2	18	10
55506695	13,5/3	21	10
55506655	16	21	10
55506665	21	28	10
55506675	29	34	10
55506685	36	42	2
55506695	48/1	54	2
55506705	48/2	67	2
SILVYN® FPAG PG grey			
55506580	7	10	10
55506590	9/1	10	10
55506600	9/2	13	10
55506610	9/3	16	10
55506620	11	16	10
55506630	13,5/1	16	10
55506640	13,5/2	18	10
55506990	13,5/3	21	10
55506650	16	21	10
55506660	21	28	10
55506670	29	34	10
55506680	36	42	2
55506690	48/1	54	2
55506700	48/2	67	2

Article number	PG size	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAG 90° PG black			
55506715	7	10	10
55506725	9	13	10
55506735	11	16	10
55506745	13,5/1	16	10
55506755	13,5/2	18	10
55506815	13,5/3	21	10
55506765	16	21	10
55506775	21	28	10
55506785	29	34	10
55506795	36	42	1
55506805	48/1	54	1
55506825	48/2	67	1
SILVYN® FPAG 90° PG grey			
55506710	7	10	10
55506720	9	13	10
55506730	11	16	10
55506740	13,5/1	16	10
55506750	13,5/2	18	10
55506810	13,5/3	21	10
55506760	16	21	10
55506770	21	28	10
55506780	29	34	10
55506790	36	42	1
55506800	48/1	54	1
55506820	48/2	67	1

Photographs are not to scale and do not represent detailed images of the respective products.

Accessories

- SKINTOP® GMP-GL refer to page 812