



X-Lock cup brushes		knotted				crimped					
D	B	H	Z	ZF	RPM	Pack.	STH 0,50	ROF 0,50	STA 0,35	ROF 0,35	
mm inch	mm inch	mm inch			max.		Art.-No.	Art.-No.	Art.-No.	Art.-No.	
1	85 3 3/8	12 1/2	20 13/16	20	B	11.500	1	483.21X	483.81X		
2	85 3 3/8	16 5/8	22 7/8	-	-	12.500	1			423.16X	423.36X

X-Lock bevel brushes		knotted				crimped					
D	B	H	Z	ZF	RPM	Pack.	STH 0,50	ROF 0,50	STA 0,35	ROF 0,35	
mm inch	mm inch	mm inch			max.		Art.-No.	Art.-No.	Art.-No.	Art.-No.	
3	115 4 1/2	12 1/2	24 15/16	20	B	15.000	1	472.25X	472.85X		
4	115 4 1/2	16 5/8	20 13/16	-	-	15.000	1			423.17X	423.37X

X-Lock wheel brushes knotted						STH 0,50		ROH 0,50	
D	B	H	Z	ZF	RPM	Pack.	Art.-No.	Art.-No.	Art.-No.
mm inch	mm inch	mm inch			max.				
5	115 4 1/2	14 9/16	23,5 15/16	20	B	12.500	1	472.21X	472.81X
	125 4 15/16	14 9/16	28,5 1 1/8	20	B	15.000	1	473.21X	473.81X

X-Lock pipeline brushes knotted						STH 0,50		ROH 0,50	
D	B	H	Z	ZF	RPM	Pack.	Art.-No.	Art.-No.	Art.-No.
mm inch	mm inch	mm inch			max.				
6	115 4 1/2	6 1/4	21,5 7/8	32	D	15.000	1	472.20X.32	472.80X.32
	125 4 15/16	6 1/4	26,5 1 1/16	40	D	15.000	1	473.20X.40	473.80X.40