

Hand Brushes Standard



II/III
EAN

Hand Brushes

	Rows >	1	2	3	4	5	6	
Filling	Pack.	Art.-No.	Art.-No.	Art.-No.	Art.-No.	Art.-No.	Art.-No.	
1	STA straight 0.35 0.014"	12	100.011	100.021	100.031	100.041	100.051	100.061
	STA straight 0.35 0.014"	100		100.020	100.030	100.040	100.050	
	STM crimped 0.30 0.012"	12		105.421	105.431	105.441	105.451	<i>105.461</i>
	STA crimped 0.20 0.008"	12			102.431	102.441		
	STA crimped 0.30 0.012"	12	102.611	102.621	102.631	102.641	102.651	102.661
2	ROF crimped 0.15 0.006"	12		104.321	104.331	104.341		
	ROF crimped 0.20 0.008"	12		104.421	104.431	104.441	104.451	
	ROF crimped 0.35 0.014"	12	104.611	104.621	104.631	104.641	104.651	104.661
	ROF straight 0.35 0.014"	12	103.711	103.721	103.731	103.741	103.751	103.761
	RO8 straight 0.30 0.012"	12			105.731	105.741		
3	MES crimped 0.15 0.006"	12		107.321	107.331	107.341	107.351	
	MES crimped 0.25 0.010"	12	<i>107.411</i>	107.421	107.431	107.441	107.451	<i>107.461</i>
	MES crimped 0.35 0.014"	12	<i>107.611</i>	107.621	107.631	107.641	107.651	107.661
	MES straight 0.35 0.014"	12		106.621	106.631	106.641	106.651	
4	BRO crimped 0.20 0.008"	12			<i>108.331</i>	108.341	<i>108.351</i>	
	BRO crimped 0.40 0.016"	12				<i>108.041</i>		
	PA straight 0.40 0.016"	12			109.431	109.441	109.451	
4	FIB	12				109.741		

Other filling materials and trim length on request.

Item Nos. in bold are available ex stock.
Consider our minimum order value for *italic printed* article numbers (see page 178).

STA = steel wire

STM = brass coated steel

ROF = stainless steel wire

RO8 = stainless steel wire, extremely heat resistant

MES = brass wire

BRO = bronze wire

PA = polyamide

FIB = fibre



Promoting sustainable forest management
www.pefc.de