

























IMG	CODE	MATERIAL	DIMENSIONS	FLUX DENSITY	ATTRACTIVE FORCE
	NDC0004	Neodymium	Φ30mmXΦ5.3mmX5mm/M5	188.9mT	8.11kgf
	NDC0123	Neodymium	Φ30mmXΦ5.3mmX10mm/M5	331.4mT	13.2kgf
	NDC0005	Neodymium	Φ30mmXΦ5.3mmX15mm/M5	422.4mT	18.8kgf
	NDC0128	Neodymium	Φ30mmXΦ10.5mmX15mm/M10	422.4mT	17kgf
	NDC0006	Neodymium	Φ35mmXΦ5.3mmX5mm/M5	164.1mT	9.46kgf
	NDE0002	Neodymium	Φ3mmX2.5mm EPOXY	366.3mT	0.285kgf
	NDE0008	Neodymium	Φ3.5mmX3mm EPOXY	387.1mT	0.394kgf
	NDE0371	Neodymium	Φ4mmX4 mm EPOXY	534.4mT	0.552kgf
	NDE0003	Neodymium	Φ10mmX2mm EPOXY	203.9mT	1.07kgf
	NDD0001	Neodymium	Φ1mmX2.5mm GOLD Dia	148.5mT	0.016kgf
	NDD0002	Neodymium	Φ2mmX5mm Dia	302.6mT	0.128kgf
	NDD0003	Neodymium	Φ2mmX6mm Dia	297.6mT	0.147kgf
	NDD0004	Neodymium	Φ3mmX5mm Dia	389.2mT	0.258kgf
	NDD0005	Neodymium	Φ4mmX3mm Dia	437.9mT	0.271kgf
	NDD0013	Neodymium	Φ4mmX5mm Dia	442mT	0.406kgf
	NDD0007	Neodymium	Φ5mmX3mm Dia	466.5mT	0.37kgf
	NDD0008	Neodymium	Φ5mmX5mm Dia	477mT	0.565kgf
	NDD0009	Neodymium	Φ5mmX10mm Dia	452.4mT	0.948kgf
	NDD0010	Neodymium	Φ5mmX15mm Dia	432.9mT	1.29kgf
	NDD0011	Neodymium	Φ6mmX3mm Dia	485.9mT	0.472kgf
	NDD0012	Neodymium	Φ7mmX5mm Dia	519.9mT	0.899kgf
	NDD0006	Neodymium	Φ8mmX1mm Dia	348.6mT	0.225kgf
	NR0103	Neodymium	Φ4mmXΦ2mmX1.5mm	227.8mT	0.285kgf
	NR0097	Neodymium	Φ4mmXΦ2mmX4mm	284.7mT	0.392kgf