

# Conventional V-Belts for ARPM / RMA IP-20 Wrapped Type / Raw Edge Cogged Type

## Standard Belt Sizes

C,CX							
Belt Code	Inside length Li (mm)	Outside length (mm)	Outside Length (In.)	Belt Code	Inside length Li (mm)	Outside length (mm)	Outside Length (In.)
40	1016	1119	44.1	102	2591	2692.4	106.0
42	1067	1169	46.0	105	2667	2768.6	109.0
45	1143	1244	49.0	108	2743	2844.8	112.0
48	1219	1324	52.1	110	2794	2895.6	114.0
50	1270	1374	54.1	112	2845	2946.4	116.0
51	1295	1399	55.1	115	2921	3022.6	119.0
52	1321	1424	56.1	118	2997	3098.8	122.0
53	1346	1449	57.0	120	3048	3149.6	124.0
54	1372	1474	58.0	122	3099	3200.4	126.0
55	1397	1499	59.0	125	3175	3276.6	129.0
56	1422	1524	60.0	128	3251	3352.8	132.0
57	1448	1549	61.0	130	3302	3403.6	134.0
58	1473	1574	62.0	132	3353	3454.4	136.0
59	1499	1599	63.0	135	3429	3530.6	139.0
60	1524	1629	64.1	138	3505	3606.8	142.0
61	1549	1654	65.1	140	3556	3657.6	144.0
62	1575	1679	66.1	142	3607	3708.4	146.0
63	1600	1704	67.1	145	3683	3784.6	149.0
64	1626	1729	68.1	148	3759	3860.8	152.0
65	1651	1754	69.1	150	3810	3911.6	154.0
66	1676	1779	70.0	155	3937	4038.6	159.0
67	1702	1804	71.0	160	4064	4165.6	164.0
68	1727	1829	72.0	165	4191	4292.6	169.0
69	1753	1854	73.0	170	4318	4419.6	174.0
70	1778	1879	74.0	180	4572	4673.6	184.0
71	1803	1904	75.0	190	4826	4927.6	194.0
72	1829	1934	76.1	200	5080	5181.6	204.0
73	1854	1959	77.1	210	5334	5435.6	214.0
74	1880	1984	78.1	220	5588	5689.6	224.0
75	1905	2009	79.1	230	5842	5943.6	234.0
76	1930	2034	80.1	240	6096	6197.6	244.0
77	1956	2059	81.1	250	6350	6451.6	254.0
78	1981	2084	82.0	260	6604	6705.6	264.0
79	2007	2109	83.0	270	6858	6959.6	274.0
80	2032	2134	84.0				
81	2057	2159	85.0				
82	2083	2184	86.0				
83	2108	2209	87.0				
84	2134	2234	88.0				
85	2159	2264	89.1				
86	2184	2289	90.1				
87	2210	2311	91.0				
88	2235	2339	92.1				
89	2261	2362	93.0				
90	2286	2389	94.1				
91	2311	2414	95.0				
92	2337	2440	96.1				
93	2362	2464	97.0				
94	2388	2489	98.0				
95	2413	2514	99.0				
96	2438	2539	100.0				
97	2464	2565	101.0				
98	2489	2591	102.0				
99	2515	2616	103.0				
100	2540	2642	104.0				

Size range: 37" ~ 660"

: Available size for Raw Edge Cogged V-Belts CX