

給湯用銅管継手

※冷媒サイズはカタログ163頁に掲載しています。

銅管エルボ(45°)

MK148K MB



寸法(d)	呼び径	L	価格	入数
12.70	3/8	15.5	170	100/1000
15.88	1/2	19	170	100/1000
22.22	3/4	27	390	60/600
28.58	1	33	690	30/300
34.92	1 1/4	37	1,300	20/200
41.28	1 1/2	47	1,800	10/100
53.98	2	60	3,600	4/40
66.68	2 1/2	80	11,200	3/30
79.38	3	88	15,200	2/20
104.78	4	111	30,000	2

※材質：リン酸銅

銅管内ネジアダプタ

M153 MB



寸法(d)	Rc	L	価格	入数
9.52	1/4	23	840	100
12.70	3/8	24	540	100/1000
15.88	1/2	30	430	50/500
22.22	3/4	35	690	40/400
28.58	1	42	1,480	20/200
34.92	1 1/4	48	2,460	10/100
41.28	1 1/2	51	3,040	10/100
53.98	2	63	6,160	5/50
66.68	2 1/2	75	15,600	4/40
79.38	3	83	23,800	2/20
1 1/2×12.70	1 1/2	29	690	50/500
1 1/2×22.22	1 1/2	35	680	40/400

※材質：リン酸銅

銅管外ネジアダプタ

M154 MB



寸法(d)	R	L	価格	入数
9.52	1/4	21	640	100
12.70	3/8	24	600	100/1000
15.88	1/2	29	340	50/500
22.22	3/4	34	600	40/400
28.58	1	40	1,080	30/300
34.92	1 1/4	46	2,060	10/100
41.28	1 1/2	51	2,680	10/100
53.98	2	60	5,400	5/50
66.68	2 1/2	70	14,200	4/40
79.38	3	77	21,600	3/30
1 1/2×12.70	1 1/2	28	540	50/500
1 1/2×22.22	1 1/2	35	930	40/400

※材質：リン酸銅

銅管キャップ

M154K MB



寸法(d)	呼び径	H(深さ)	価格	入数
12.70	3/8	3.5	88	100/1000
15.88	1/2	6	110	25/250
※ 19.05	冷媒3/4	5.2	250	20/200
22.22	3/4	6.5	140	20/200
※ 25.40	冷媒1	5.5	460	25/250
28.58	1	7	230	25/250
34.92	1 1/4	8	350	10/100
41.28	1 1/2	8	540	5/50
53.98	2	9	1,020	3/30
66.68	2 1/2	12	2,760	3/30
79.38	3	18	7,820	2/20
104.78	4	23	17,000	1

※材質：リン酸銅 ※冷媒管サイズです。

銅管キャップ(深型)

MK154KF MB



寸法(d)	呼び径	H(深さ)	価格	入数
15.88	1/2	14.5	160	25/250
22.22	3/4	22	250	20/200
28.58	1	22	430	20
34.92	1 1/4	25	600	10
41.28	1 1/2	28	1,260	10
53.98	2	35	1,460	10
66.68	2 1/2	39	4,480	1
79.38	3	44	9,820	1
104.78	4	56	21,400	1

※材質：リン酸銅