

## 砲金継手・真鍮継手

### 砲金六角回転ブッシング

#### M154BMNK MB



寸法	d <sub>1</sub>	d <sub>2</sub>	φd	L <sub>1</sub>	L <sub>2</sub>	価格	入数
13	Rc1/2	R1/2	12.3	17	27	1,640	10/50
20	Rc3/4	R3/4	17.3	19	31	2,160	5/25
20×13	Rc3/4	R1/2	12.3	19	27	2,160	5/25

※材質：青銅製

### 砲金六角回転ニップル

#### M154MNMK MB



寸法	d <sub>1</sub>	φd	L <sub>1</sub>	L <sub>2</sub>	価格	入数
13	R1/2	12.3	21	27	1,640	10/50
20	R3/4	17.3	24	31	2,160	5/25

※材質：青銅製

### 砲金六角回転ソケット

#### M150MNMK MB



寸法	d <sub>1</sub>	φd	L <sub>1</sub>	L <sub>2</sub>	価格	入数
13	Rc1/2	12.3	17	27	1,640	10/50
20	Rc3/4	17.3	19	31	2,160	5/25

※材質：青銅製

#### 回転継手説明

■特長  
左右のねじが  
回転自在の継手  
ねじ部がそれぞれ独立  
して回転しますので、  
相手物どうしを回転  
させずに配管できます。

#### 施工例



注意 ガス・灯油等の油類には使用できません。回転・傾動を目的とした配管には使用できません。

### 真鍮ソケット

#### M150N MB



寸法 Rc×Rc	L	価格	入数
3 (1/8)	21	230	10/100
6 (1/4)	28	380	10/100
10 (3/8)	32	550	10/100
13 (1/2)	40	660	10/100
20 (3/4)	49	1,280	10/50
3×6 (1/8×1/4)	28	550	10/100
6×10 (1/4×3/8)	32	700	10/100
6×13 (1/4×3/8)	40	1,760	10/100
10×13 (3/8×1/2)	40	1,900	10/100
13×20 (1/2×3/4)	44	2,000	10/50

※材質：真鍮製

### 真鍮内・外ネジソケット

#### M150NB MB



寸法 Rc×R	L	価格	入数
3 (1/8×1/8)	23	420	10
6 (1/4×1/4)	26	490	10
10 (3/8×3/8)	29	850	10
13 (1/2×1/2)	34	1,460	10
20 (3/4×3/4)	37	2,440	10
25 (1×1)	45	3,600	10
3×6 (1/8×1/4)	23	280	10
6×3 (1/4×3/8)	24	280	10
6×10 (1/4×3/8)	24	490	10
6×13 (1/4×3/8)	30	940	10
10×3 (3/8×1/8)	26	490	10
10×6 (3/8×1/4)	28	490	10
10×13 (3/8×1/2)	31	920	10
13×3 (1/2×1/8)	29	940	10
13×6 (1/2×1/4)	31	940	10
13×10 (1/2×3/8)	31	940	10
13×20 (1/2×3/4)	34	1,200	10
20×13 (3/4×1/2)	36	1,120	10
25×20 (1×3/4)	40	2,320	10

※材質：真鍮製

### 真鍮ニップル

#### M154N MB



寸法 R×R	L	価格	入数
3 (1/8×1/8)	25	160	10/100
6 (1/4×1/4)	30	170	10/100
10 (3/8×3/8)	33	240	10/100
13 (1/2×1/2)	41	400	10/100
20 (3/4×3/4)	44	940	10/100
25 (1×1)	52	2,000	5/50
3×6 (1/8×1/4)	28	200	10/100
3×10 (1/8×3/8)	30	320	10/100
3×13 (1/8×3/8)	34	1,000	10/100
6×10 (1/4×3/8)	31	270	10/100
6×13 (1/4×3/8)	34	410	10/100
10×13 (3/8×1/2)	36	410	10/100
13×20 (1/2×3/4)	45	1,000	10/100
20×25 (3/4×1)	52	2,200	5/50

※材質：真鍮製

### 真鍮ブッシング

#### M154NB MB



寸法 R×Rc	L	価格	入数
6×3 (1/4×1/8)	15	240	10/100
10×3 (3/8×1/8)	16	340	10/100
10×6 (3/8×1/4)	16	340	10/100
13×3 (1/2×1/8)	18	630	10/100
13×6 (1/2×1/4)	18	630	10/100
13×10 (1/2×3/8)	18	630	10/100
20×10 (3/4×1/2)	21	1,000	10/100
20×13 (3/4×1/2)	21	1,000	10/100
25×13 (1×1/2)	26	2,200	5/50
25×20 (1×3/4)	26	2,200	5/50

※材質：真鍮製

### 真鍮キャップ

#### M154NK MB



寸法	H	W	価格	入数
6 (1/4)	11	16	620	10/100
10 (3/8)	14	21	800	10/100

※材質：真鍮製

### 真鍮プラグ

#### M133B MB



寸法	L	W	価格	入数
3 (1/8)	15	7	240	10/100
6 (1/4)	19	9	300	10/100
10 (3/8)	21	12	360	10/100
13 (1/2)	23	14	450	10/100
20 (3/4)	29	17	800	10/100
25 (1)	30	19	1,180	5/50

※材質：真鍮製