

CABLE STRIPPERS

CST110

Improvement of type CST100

Safety cover is attached. It can smoothen the discharge of waste.



CST110 specification

Model	Length (mm)	Weight (kg)	Height (mm)	Width (mm)	Air consumption (cm ³ /stroke)	Air pressure (MPa)	Stripping capacity ϕ (mm)	Stripping length (mm)
CST110	470	21	200	275	3,100	0.5~0.6	up to ϕ 15mm outer dia.	100

CST100L

Long type

It is suitable for stripping long dimension cable.



CST100L specification

Model	Length (mm)	Weight (kg)	Height (mm)	Width (mm)	Air consumption (cm ³ /stroke)	Air pressure (MPa)	Stripping capacity ϕ (mm)	Stripping length (mm)
CST100L	785	18	155	300	5,872	0.5~0.6	up to ϕ 15mm outer dia.	200

CST120

Large type

It is suitable for stripping of large diameter cable.



CST120 specification

Model	Length (mm)	Weight (kg)	Height (mm)	Width (mm)	Air consumption (cm ³ /stroke)	Air pressure (MPa)	Stripping capacity ϕ (mm)	Stripping length (mm)
CST120	487	43	282.5	493	8,000	0.5~0.6	up to ϕ 30mm outer dia.	100