




ソケット 鉄スリーブ


SH(ホースニップル形)



品番	適用ホース	寸			法 (mm)				重量 (g)
		L	φD	S	C	ℓ	φB	φT	
* CAT22SH	1/4"	75.5	26.5	19	21.5	30	5	9	106
* CAT23SH	3/8"	79.5	26.5	19	21.5	34	7.5	11.3	108
* CAT24SH	1/2"	81.5	26.5	19	21.5	36	9	15	120

※標準品


SM(オネジ形)



品番	接続形状 T	寸			法 (mm)				重量 (g)
		L	φD	S	C	φB	φT		
* CAT22SM	R1/4"	58.5	26.5	19	21.5	7	103		
* CAT23SM	R3/8"	59.5	26.5	19	21.5	8	110		
* CAT24SM	R1/2"	61.5	26.5	22	25	9	129		

※標準品


SF(メネジ形)



品番	接続形状 T	寸			法 (mm)				重量 (g)
		L	φD	S	C	φB	φT		
* CAT22SF	Rc1/4"	53.5	26.5	19	21.5	104			
* CAT23SF	Rc3/8"	53.5	26.5	21	24	104			
* CAT24SF	Rc1/2"	55.5	26.5	29	33.5	143			

※標準品


S A・S B(ポリウレタンチューブ用)



品番	適用ホース φ外径×φ内径	寸			法 (mm)				重量 (g)
		L	φD	H ₁	H ₂	ℓ	φB		
* CAT21SA	8×5	60.5	26.5	19	14	15	4	98	
* CAT22SA	9×6	62.5	26.5	19	17	17	4.8	115	
* CAT22SB	10×6.5	62.5	26.5	19	17	17	5.3	114	
* CAT23SA	12×8	65.5	26.5	19	19	20	7	124	
* CAT23SB	12.5×8.5	64.5	26.5	19	19	19	7	121	
* CAT24SA	16×11	69.5	26.5	23	27	25	10	166	

※標準品

S A R・S B R(ロータリー・ポリウレタンチューブ用)




品番	適用ホース φ外径×φ内径	寸			法 (mm)				重量 (g)
		L	φD	H ₁	H ₂	ℓ	φB		
* CAT22SBR	10×6.5	67	26.5	19	17	17	5.3	124	
* CAT23SAR	12×8	70	26.5	19	19	20	7	134	

※標準品


ソケット 樹脂スリーブ

SH(ホースニップル形)




品番	適用ホース	寸			法 (mm)				重量 (g)
		L	φD	S	C	ℓ	φB	φT	
CAT21SH-N	1/8"	75.5	26.5	19	21.5	30	4.5	7.5	85
CAT22SH-N	1/4"	75.5	26.5	19	21.5	30	5	9	88
CAT23SH-N	3/8"	79.5	26.5	19	21.5	34	7.5	11.3	90
CAT24SH-N	1/2"	81.5	26.5	19	21.5	36	9	15	102

SM(オネジ形)




品番	接続形状 T	寸			法 (mm)				重量 (g)
		L	φD	S	C	φB	φT		
CAT21SM-N	R1/8"	55.5	26.5	19	21.5	4	83		
CAT22SM-N	R1/4"	58.5	26.5	19	21.5	7	85		
CAT23SM-N	R3/8"	59.5	26.5	19	21.5	8	92		
CAT24SM-N	R1/2"	61.5	26.5	22	25	9	111		

SF(メネジ形)




品番	接続形状 T	寸			法 (mm)				重量 (g)
		L	φD	S	C	φB	φT		
CAT21SF-N	Rc1/8"	50.5	26.5	19	21.5	85			
CAT22SF-N	Rc1/4"	53.5	26.5	19	21.5	86			
CAT23SF-N	Rc3/8"	53.5	26.5	21	24	86			
CAT24SF-N	Rc1/2"	55.5	26.5	29	33.5	125			

S A・S B(ポリウレタンチューブ用)



品番	適用ホース φ外径×φ内径	寸			法 (mm)				重量 (g)
		L	φD	H ₁	H ₂	ℓ	φB		
CAT21SA-N	8×5	60.5	26.5	19	14	15	4	80	
CAT22SA-N	9×6	62.5	26.5	19	17	17	4.8	97	
CAT22SB-N	10×6.5	62.5	26.5	19	17	17	5.3	96	
CAT23SA-N	12×8	65.5	26.5	19	19	20	7	106	
CAT23SB-N	12.5×8.5	64.5	26.5	19	19	19	7	103	
CAT24SA-N	16×11	69.5	26.5	23	27	25	10	148	

S A R・S B R(ロータリー・ポリウレタンチューブ用)



品番	適用ホース φ外径×φ内径	寸			法 (mm)				重量 (g)
		L	φD	H ₁	H ₂	ℓ	φB		
* CAT22SBR-N	10×6.5	67	26.5	19	17	17	5.3	106	
* CAT23SAR-N	12×8	70	26.5	19	19	20	7	116	

※標準品

*ご使用前に、クイックカップリングの取扱上の注意を必ずお読み下さい。